

MODLINK MSDD DATA INSERT

2xUSB-A female/female + 1xRJ45

Art.No.: 4000-68000-0960000
Weight: 0.069 kg
Country of origin: DE
Model designation: FR.Modul 1 x RJ45 + 2 x USB Bu/Bu

RJ45; USB; USB (A)
1 x RJ45, 8-pole metal, CAT5e (female/female)
2 x USB (female/female) form A

Link to Product

Illustration



Product may differ from Image



Header

Material short textFR.Modul 1 x RJ45 + 2 x USB Bu/Bu

Commercial data

URL Webshop	https://shop.murrelektronik.com/4000-68000-0960000
GTIN	4048879037785
ECLASS-6.0	27189217
ECLASS-6.1	27189217
ECLASS-7.0	27189217
ECLASS-7.1	27189217
ECLASS-8.0	27189217
ECLASS-8.1	27189217
ECLASS-9.0	27182806
ECLASS-9.1	27189217
ECLASS-10.0.1	27182806
ECLASS-10.1	27182806
ECLASS-11.0	27182806
ECLASS-11.1	27182806
ECLASS-12.0	27182806
ECLASS-13.0	27182806

ECLASS-14.0	27182806
ETIM-5.0	EC002625
ETIM-6.0	EC002625
ETIM-7.0	EC002625
ETIM-8.0	EC002625
customs tariff number	85366990
EAN	4048879037785
Packaging unit	1

Mechanical data | Mounting data

Height	88 mm
Width	51 mm
Depth	60 mm

Environmental characteristics | Climatic

Ambient temperature (storage, transport)	-20 °C
--	--------

Shielding plate

Connection information	Threaded hole M4
Tightening torque	0,9 Nm
Tightening torque tolerance	± 0,1 Nm

USB

USB specification	2.0
Looking techniques	Snap-in connector
Data transmission rate max.	480 Mbit/s
Operating voltage AC	48 V
Operating voltage DC	48 V
Operating current max.	500 mA
Operating voltage DC (UL-listed)	42,4 V

RJ45

Family construction form	RJ45
Looking techniques	Snap-in connector
Cable category min.	Cat5e
Family type Back side	RJ45
Operating voltage AC max. (UL-listed)	30 V
Operating voltage DC max. (UL-listed)	42,4 V
Current operating max. (UL)	175 mA