

ECLASS-14.0	27182806
ETIM-5.0	EC002625
ETIM-6.0	EC002625
ETIM-7.0	EC002625
ETIM-8.0	EC002625
customs tariff number	85444290
EAN	4048879037761
Packaging unit	1

Mechanical data | Mounting data

Height	88 mm
Width	51 mm
Depth	45 mm

Environmental characteristics | Climatic

Ambient temperature (storage, transport)	-30 °C ... 60 °C
--	------------------

Shielding plate

Connection information	Threaded hole M4
Tightening torque	0,9 Nm
Tightening torque tolerance	± 0,1 Nm

USB

USB specification	2.0
Looking techniques	Snap-in connector
Data transmission rate max.	480 Mbit/s
Operating voltage AC	48 V
Operating voltage DC	48 V
Operating current max.	500 mA
Operating voltage DC (UL-listed)	42,4 V

RJ45

Family construction form	RJ45
Looking techniques	Snap-in connector
Cable category min.	Cat5e
Family type Back side	RJ45
Operating voltage AC max. (UL-listed)	30 V
Operating voltage DC max. (UL-listed)	42,4 V
Current operating max. (UL)	175 mA