

MODLINK MSDD DATA INSERT

1xSUB-D25 female/female + 1xRJ45 + 1xRJ12

Art.No.: 4000-68000-1100000
Weight: 0.039 kg
Country of origin: DE
Model designation: FR.MODUL 25pol.Bu/St+RJ45/45+RJ12/12

RJ45; RJ12; SUB-D25
1× RJ45, 8-pole metal, CAT5e (female/female)
1× RJ12 (6-pole plastic)
1× SUB-D25 (female/male)

Link to Product

Illustration



Product may differ from Image



Header	
Material short text	FR.MODUL 25pol.Bu/St+RJ45/45+RJ12/12
Commercial data	
URL Webshop	https://shop.murrelektronik.com/4000-68000-1100000
GTIN	4048879037693
ECLASS-6.0	27189217
ECLASS-6.1	27189217
ECLASS-7.0	27189217
ECLASS-7.1	27189217
ECLASS-8.0	27189217
ECLASS-8.1	27189217
ECLASS-9.0	27182806
ECLASS-9.1	27189217
ECLASS-10.0.1	27182806
ECLASS-10.1	27182806
ECLASS-11.0	27182806
ECLASS-11.1	27182806
ECLASS-12.0	27182806

ECLASS-13.0	27182806
ECLASS-14.0	27182806
ETIM-5.0	EC002625
ETIM-6.0	EC002625
ETIM-7.0	EC002625
ETIM-8.0	EC002625
customs tariff number	85366990
EAN	4048879037693
Packaging unit	1

Mechanical data | Mounting data

Height	88 mm
Width	51 mm
Depth	25 mm

Environmental characteristics | Climatic

Ambient temperature (storage, transport)	-20 °C ... 60 °C
--	------------------

SUB-D25

Family construction form	SUB-D25
Gender	female
No. of poles	25
Looking techniques	Standard UNC 4-40 screw thread bolt (EN 60807)
Family type Back side	SUB-D25
Gender Rear	male
Operating voltage AC	48 V
Operating voltage DC	48 V
Operating current	3 A
Operating voltage AC max. (UL-listed)	30 V
Operating voltage DC max. (UL-listed)	42,4 V
Current operating max. (UL)	175 mA

RJ12

Family construction form	RJ12
Looking techniques	Snap-in connector
Family type Back side	RJ12
Operating voltage AC max.	48 V
Operating voltage DC max.	48 V
Operating current max.	1 A
Operating voltage AC max. (UL-listed)	30 V
Operating voltage DC max. (UL-listed)	42,4 V
Current operating max. (UL)	175 mA

RJ45

Family construction form	RJ45
Looking techniques	Snap-in connector
Cable category min.	Cat5e
Family type Back side	RJ45
Operating voltage AC max. (UL-listed)	30 V
Operating voltage DC max. (UL-listed)	42,4 V
Current operating max. (UL)	175 mA