

MODLINK MSDD DATA INSERT

1×SUB-D9 fem./fem. + 1×SUB-D9 male/male + 1×RJ45

Art.No.: 4000-68000-1110000
Weight: 0.045 kg
Country of origin: DE
Model designation: FR.MODUL 9Bu/Bu+9St/St+RJ45/45

RJ45; SUB-D9; SUB-D9
1× RJ45, 8-pole metal, CAT5e (female/female)
1× SUB-D9 (female/female)
1× SUB-D9 (male/male)

Link to Product

Illustration



Product may differ from Image



Header

Material short textFR.MODUL 9Bu/Bu+9St/St+RJ45/45

Commercial data

URL Webshop	https://shop.murrelektronik.com/4000-68000-1110000
GTIN	4048879037686
ECLASS-6.0	27189217
ECLASS-6.1	27189217
ECLASS-7.0	27189217
ECLASS-7.1	27189217
ECLASS-8.0	27189217
ECLASS-8.1	27189217
ECLASS-9.0	27182806
ECLASS-9.1	27189217
ECLASS-10.0.1	27182806
ECLASS-10.1	27182806
ECLASS-11.0	27182806
ECLASS-11.1	27182806
ECLASS-12.0	27182806

ECLASS-13.0	27182806
ECLASS-14.0	27182806
ETIM-5.0	EC002625
ETIM-6.0	EC002625
ETIM-7.0	EC002625
ETIM-8.0	EC002625
customs tariff number	85366990
EAN	4048879037686
Packaging unit	1

Mechanical data | Mounting data

Height	88 mm
Width	51 mm
Depth	21 mm

Environmental characteristics | Climatic

Ambient temperature (storage, transport)	-10 °C
--	--------

SUB-D9

Family construction form	SUB-D9
Gender	female
No. of poles	9
Looking techniques	Standard UNC 4-40 screw thread bolt (EN 60807)
Family type Back side	SUB-D9
Gender Rear	female
Operating voltage AC	48 V
Operating voltage DC	48 V
Operating current	3 A
Operating voltage AC max. (UL-listed)	30 V
Operating voltage DC max. (UL-listed)	42,4 V
Current operating max. (UL)	175 mA

RJ45

Family construction form	RJ45
Looking techniques	Snap-in connector
Cable category min.	Cat5e
Family type Back side	RJ45
Operating voltage AC max. (UL-listed)	30 V
Operating voltage DC max. (UL-listed)	42,4 V
Current operating max. (UL)	175 mA