

MODLINK MSDD DATA INSERT

1xSUB-D9 cut-out + 1xRJ45 + 2xUSB-A fem/male 0,7m
Art.No.: 4000-68000-1250000
Weight: 0.137 kg
Country of origin: DE
Model designation: Fr. Module 1xSUB-D9cutout+1xRJ45+2xUSB

RJ45; USB; USB (A); SUB-D9 (cut-out)
1× RJ45, 8-pole metal, CAT5e (female/female)
2× USB (female/female) form A
1× SUB-D9 cut-out

Link to Product

Illustration



Product may differ from Image



Header	
Material short text	Fr. Module 1xSUB-D9cutout+1xRJ45+2xUSB
Commercial data	
URL Webshop	https://shop.murrelektronik.com/4000-68000-1250000
GTIN	4048879290388
ECLASS-6.0	27189217
ECLASS-6.1	27189217
ECLASS-7.0	27189217
ECLASS-7.1	27189217
ECLASS-8.0	27189217
ECLASS-8.1	27189217
ECLASS-9.0	27182806
ECLASS-9.1	27189217
ECLASS-10.0.1	27182806
ECLASS-10.1	27182806
ECLASS-11.0	27182806
ECLASS-11.1	27182806
ECLASS-12.0	27182806

ECLASS-13.0	27182806
ECLASS-14.0	27182806
ETIM-5.0	EC002625
ETIM-6.0	EC002625
ETIM-7.0	EC002625
ETIM-8.0	EC002625
customs tariff number	85366990
EAN	4048879290388
Packaging unit	1

Mechanical data | Mounting data

Height	88 mm
Width	51 mm
Depth	45 mm

Environmental characteristics | Climatic

Ambient temperature (storage, transport)	5 °C ... 40 °C
--	----------------

USB

USB specification	2.0
Looking techniques	Snap-in connector
Data transmission rate max.	480 Mbit/s
Operating voltage AC	48 V
Operating voltage DC	48 V
Operating current max.	500 mA
Operating voltage DC (UL-listed)	42,4 V

RJ45

Family construction form	RJ45
Looking techniques	Snap-in connector
Cable category min.	Cat5e
Family type Back side	RJ45
Operating voltage AC max. (UL-listed)	30 V
Operating voltage DC max. (UL-listed)	42,4 V
Current operating max. (UL)	175 mA