

MODLINK MSDD DATA INSERT

2×USB-A female/female + 1×DVI

Art.No.: 4000-68000-1280000
Weight: 0.072 kg
Country of origin: TW
Model designation: FR.MODUL 2xUSB+DVI

USB (form A); DVI
2× USB (female/female) form A
1× DVI (female/female)

Link to Product

Illustration



Product may differ from Image



Header

Material short textFR.MODUL 2xUSB+DVI

Commercial data

URL Webshop	https://shop.murrelektronik.com/4000-68000-1280000
GTIN	4048879355643
ECLASS-6.0	27189217
ECLASS-6.1	27189217
ECLASS-7.0	27189217
ECLASS-7.1	27189217
ECLASS-8.0	27189217
ECLASS-8.1	27189217
ECLASS-9.0	27182806
ECLASS-9.1	27189217
ECLASS-10.0.1	27182806
ECLASS-10.1	27182806
ECLASS-11.0	27182806
ECLASS-11.1	27182806
ECLASS-12.0	27182806
ECLASS-13.0	27182806

ECLASS-14.0	27182806
ETIM-5.0	EC002625
ETIM-6.0	EC002625
ETIM-7.0	EC002625
ETIM-8.0	EC002625
customs tariff number	85366990
EAN	4048879355643
Packaging unit	1

Mechanical data | Mounting data

Height	88 mm
Width	51 mm
Depth	45 mm

Environmental characteristics | Climatic

Ambient temperature (storage, transport)	5 °C
--	------

Shielding plate

Connection information	Threaded hole M4
Tightening torque	0,9 Nm
Tightening torque tolerance	± 0,1 Nm

USB

USB specification	2.0
Looking techniques	Snap-in connector
Data transmission rate max.	480 Mbit/s
Operating voltage AC	48 V
Operating voltage DC	48 V
Operating current max.	500 mA
Operating voltage DC (UL-listed)	42,4 V

DVI

Gender	female
Family type Back side	DVI
Gender Rear	female
Operating voltage AC max.	40 V
Operating current max.	1,5 A