

MODLINK MSDD DATA INSERT

1×SUB-D9 fem./male+ 1×RJ45+ 1×USB-A fem./male 0,7m
Art.No.: 4000-68000-1400000
Weight: 0.082 kg
Country of origin: DE
Model designation: FR.MODUL 9POL.BU/ST+RJ45/45+USBGESCH.

USB (form A); SUB-D9; RJ45
1× USB 2.0 (female/female/0.7 m cable) form A
1× SUB-D9 (female/male)
1× RJ45, 8-pole metal, CAT5e (female/female)

Link to Product

Illustration



Product may differ from Image



Header

Material short textFR.MODUL 9POL.BU/ST+RJ45/45+USBGESCH.

Commercial data

URL Webshop	https://shop.murrelektronik.com/4000-68000-1400000
GTIN	4048879037570
ECLASS-6.0	27189217
ECLASS-6.1	27189217
ECLASS-7.0	27189217
ECLASS-7.1	27189217
ECLASS-8.0	27189217
ECLASS-8.1	27189217
ECLASS-9.0	27182806
ECLASS-9.1	27189217
ECLASS-10.0.1	27182806
ECLASS-10.1	27182806
ECLASS-11.0	27182806
ECLASS-11.1	27182806
ECLASS-12.0	27182806

ECLASS-13.0	27182806
ECLASS-14.0	27182806
ETIM-5.0	EC002625
ETIM-6.0	EC002625
ETIM-7.0	EC002625
ETIM-8.0	EC002625
customs tariff number	85366990
EAN	4048879037570
Packaging unit	1
customs tariff number	85366990
EAN	4048879037570
Packaging unit	1

Mechanical data | Mounting data

Height	88 mm
Width	51 mm
Depth	45 mm

Environmental characteristics | Climatic

Ambient temperature (storage, transport)	5 °C
--	------

Shielding plate

Connection information	Threaded hole M4
Tightening torque	0,9 Nm
Tightening torque tolerance	± 0,1 Nm

USB

USB specification	2.0
Looking techniques	Snap-in connector
Data transmission rate max.	480 Mbit/s
Operating voltage AC	48 V
Operating voltage DC	48 V
Operating current max.	500 mA
Operating voltage DC (UL-listed)	42,4 V

SUB-D9

Family construction form	SUB-D9
Gender	Female
No. of poles	9
Looking techniques	Standard UNC 4-40 screw thread bolt (EN 60807)
Family type Back side	SUB-D9
Gender Rear	male
Operating voltage AC	48 V
Operating voltage DC	48 V
Operating current	3 A
Operating voltage AC max. (UL-listed)	30 V
Operating voltage DC max. (UL-listed)	42,4 V
Current operating max. (UL)	175 mA

RJ45

Family construction form	RJ45
Looking techniques	Snap-in connector
Cable category min.	Cat5e
Family type Back side	RJ45
Operating voltage AC max. (UL-listed)	30 V
Operating voltage DC max. (UL-listed)	42,4 V
Current operating max. (UL)	175 mA