

MODLINK MSDD DATA INSERT

to be discontinued - Last Time Order: 2023-03-31

Art.No.: 4000-68000-1500000

Weight: 0.037 kg

Country of origin: DE

Model designation: FR.MODUL 25 pol. Bu/St+2 x PS2

PS2; PS2; SUB-D25

2x PS2 (6-pole solder connection)

1x SUB-D25 (female/male)

[Link to Product](#)

Illustration



Product may differ from Image



Header

Material short text FR.MODUL 25 pol. Bu/St+2 x PS2

Commercial data

URL Webshop	https://shop.murrelektronik.com/4000-68000-1500000
GTIN	4048879037488
ECLASS-6.0	27189217
ECLASS-6.1	27189217
ECLASS-7.0	27189217
ECLASS-7.1	27189217
ECLASS-8.0	27189217
ECLASS-8.1	27189217
ECLASS-9.0	27182806
ECLASS-9.1	27189217
ECLASS-10.0.1	27182806
ECLASS-10.1	27182806
ECLASS-11.0	27182806
ECLASS-11.1	27182806
ECLASS-12.0	27182806
ECLASS-13.0	27182806

ECCLASS-14.0	27182806
ETIM-5.0	EC002625
ETIM-6.0	EC002625
ETIM-7.0	EC002625
ETIM-8.0	EC002625
customs tariff number	85366990
EAN	4048879037488
Packaging unit	1

Mechanical data | Mounting data

Height	88 mm
Width	51 mm
Depth	15 mm

Environmental characteristics | Climatic

Ambient temperature (storage, transport)	5 °C ... 40 °C
--	----------------

SUB-D9

Family construction form	SUB-D9
Gender	female
No. of poles	9
Looking techniques	Standard UNC 4-40 screw thread bolt (EN 60807)
Family type Back side	SUB-D9
Gender Rear	male
Operating voltage AC	48 V
Operating voltage DC	48 V
Operating current	3 A
Operating voltage AC max. (UL-listed)	30 V
Operating voltage DC max. (UL-listed)	42,4 V
Current operating max. (UL)	175 mA

SUB-D25

Family construction form	SUB-D25
Gender	female
No. of poles	25
Looking techniques	Standard UNC 4-40 screw thread bolt (EN 60807)
Family type Back side	SUB-D25
Gender Rear	male
Operating voltage AC	48 V
Operating voltage DC	48 V
Operating current	3 A
Operating voltage AC max. (UL-listed)	30 V
Operating voltage DC max. (UL-listed)	42,4 V
Current operating max. (UL)	175 mA

PS2

Family construction form	PS2
Gender	female
No. of poles	6
Looking techniques	Screw locking
Connection cross section max.	0,5 mm ²
AWG number max.	20
Family type Back side	PS2
Gender Rear	Solder connection
Operating voltage AC	30 V
Operating voltage DC	30 V
Operating current	1 A