

MODLINK MSDD SOCKET INSERT CHINA

250VAC/10A screw connection

Art.No.: 4000-68000-3250000

Weight: 0.046 kg

Country of origin: CN

Model designation: Fr.Modul-I-250-10-SC

China (CCC)

Screw terminals

with touch protection

Link to Product

Illustration



Product may differ from Image



Header	
Material short text	Fr.Modul-I-250-10-SC
Commercial data	
URL Webshop	https://shop.murrelektronik.com/4000-68000-3250000
GTIN	4048879037266
ECLASS-6.0	27189217
ECLASS-6.1	27189217
ECLASS-7.0	27189217
ECLASS-7.1	27189217
ECLASS-8.0	27189217
ECLASS-8.1	27189217
ECLASS-9.0	27182806
ECLASS-9.1	27189217
ECLASS-10.0.1	27182806
ECLASS-10.1	27182806
ECLASS-11.0	27182806
ECLASS-11.1	27182806
ECLASS-12.0	27182806
ECLASS-13.0	27182806

ECLASS-14.0	27182806
ETIM-5.0	EC000020
ETIM-6.0	EC000020
ETIM-7.0	EC000020
ETIM-8.0	EC000020
customs tariff number	85366990
EAN	4048879037266
Packaging unit	1

Mechanical data | Mounting data

Height	88 mm
Width	51 mm
Depth	25 mm

Environmental characteristics | Climatic

Ambient temperature (storage, transport)	-30 °C
--	--------

China (CCC)

Connection	Screw terminals SK
No. of poles	PE
Connections per pole	2
Protection contact present	Yes
Connection cross-section solid max.	4 mm ²
Connection cross-section stranded/fine-stranded max.	4 mm ²
Operating voltage AC	250 V
Operating current	10 A