

MODLINK MSDD SINGLE COMBI INSERT USA NEMA 5-15

1xSUD-D9 female/female + 1xRJ45 female/female

Art.No.: 4000-68000-4010000
Weight: 0.046 kg
Country of origin: DE
Model designation: Fr.Modul-AB-125-15-SO+RJ45+DB9F/F

- 1 × NEMA 5-15 (plug-solder connection)
- 1 × RJ45, 8-pole metal, CAT5e (female/female)
- 1 × SUB-D9 (female/female)

Link to Product

Illustration



Product may differ from Image



Header	
Material short text	Fr.Modul-AB-125-15-SO+RJ45+DB9F/F
Commercial data	
URL Webshop	https://shop.murrelektronik.com/4000-68000-4010000
GTIN	4048879037235
ECLASS-6.0	27189217
ECLASS-6.1	27189217
ECLASS-7.0	27189217
ECLASS-7.1	27189217
ECLASS-8.0	27189217
ECLASS-8.1	27189217
ECLASS-9.0	27182806
ECLASS-9.1	27189217
ECLASS-10.0.1	27182806
ECLASS-10.1	27182806
ECLASS-11.0	27182806
ECLASS-11.1	27182806
ECLASS-12.0	27182806
ECLASS-13.0	27182806

ECLASS-14.0	27182806
ETIM-5.0	EC000020
ETIM-6.0	EC000020
ETIM-7.0	EC000020
ETIM-8.0	EC000020
customs tariff number	85366990
EAN	4048879037235
Packaging unit	1

Mechanical data | Mounting data

Height	88 mm
Width	51 mm
Depth	30 mm

Environmental characteristics | Climatic

Ambient temperature (storage, transport)	5 °C
--	------

USA

Connection	Plug-solder connection
No. of poles	PE
Protection contact present	Yes
Operating voltage AC	125 V
Operating current	15 A
UL CCN	KCXS, KCXS7
UL-Standard	UL 943
CSA-Standard	CSA C22.2 No. 144.1-16

SUB-D9

Family construction form	SUB-D9
Gender	female
No. of poles	9
Looking techniques	Standard UNC 4-40 screw thread bolt (EN 60807)
Family type Back side	SUB-D9
Gender Rear	female
Operating voltage AC	48 V
Operating voltage DC	48 V
Operating current	3 A
Operating voltage AC max. (UL-listed)	30 V
Operating voltage DC max. (UL-listed)	42,4 V
Current operating max. (UL)	175 mA

RJ45

Family construction form	RJ45
Looking techniques	Snap-in connector
Cable category min.	Cat5e
Family type Back side	RJ45
Operating voltage AC max. (UL-listed)	30 V
Operating voltage DC max. (UL-listed)	42,4 V
Current operating max. (UL)	175 mA