

MODLINK MSDD SINGLE COMBI INSERT USA NEMA 5-15

1xRJ45 female/female + 1x3A fuse

Art.No.: 4000-68000-4070000

Weight: 0.047 kg

Country of origin: DE

Model designation: Fr.Modul-AB-125-15-SO+RJ45+fuse3A

1 × NEMA 1-15 (plug-solder connection)

1 × RJ45, 8-pole metal, CAT5e (female/female)

1 × fuse (3 A)

Link to Product**Illustration**

Product may differ from Image

**Header**

Material short text Fr.Modul-AB-125-15-SO+RJ45+fuse3A

Commercial data

URL Webshop	https://shop.murrelektronik.com/4000-68000-4070000
GTIN	4048879452762
ECLASS-6.0	27189217
ECLASS-6.1	27189217
ECLASS-7.0	27189217
ECLASS-7.1	27189217
ECLASS-8.0	27189217
ECLASS-8.1	27189217
ECLASS-9.0	27182806
ECLASS-9.1	27189217
ECLASS-10.0.1	27182806
ECLASS-10.1	27182806
ECLASS-11.0	27182806
ECLASS-11.1	27182806
ECLASS-12.0	27182806
ECLASS-13.0	27182806

ECLASS-14.0	27182806
ETIM-5.0	EC000020
ETIM-6.0	EC000020
ETIM-7.0	EC000020
ETIM-8.0	EC000020
customs tariff number	85366990
EAN	4048879452762
Packaging unit	1
customs tariff number	85366990
EAN	4048879452762
Packaging unit	1

Mechanical data | Mounting data

Height	88 mm
Width	51 mm
Depth	53 mm

Environmental characteristics | Climatic

Ambient temperature (storage, transport)	5 °C
--	------

Fuse

Operating voltage AC	250 V
Operating voltage DC	32 V
Nominal current	3 A

Shielding plate

Connection information	Threaded hole M4
Tightening torque	0,9 Nm
Tightening torque tolerance	± 0,1 Nm

USA

Connection	Plug-solder connection
No. of poles	PE
Protection contact present	Yes
Operating voltage AC	125 V
Operating current	15 A

RJ45

Family construction form	RJ45
Looking techniques	Snap-in connector
Cable category min.	Cat5e
Family type Back side	RJ45
Operating voltage AC max. (UL-listed)	30 V
Operating voltage DC max. (UL-listed)	42,4 V
Current operating max. (UL)	175 mA