

Murrelektronik Inc. | 1327 Northbrook Parkway, Suite 460 | Suwanee, GA 30024 | Fon +1 770 497-9292 | Fax +1 770 497-9391 | shop@murrinc.com | shop.murrinc.com

ECLASS-13.0	27182806
ECLASS-14.0	27182806
ETIM-5.0	EC000020
ETIM-6.0	EC000020
ETIM-7.0	EC000020
ETIM-8.0	EC000020
customs tariff number	85366990
EAN	4048879369275
Packaging unit	1

Mechanical data | Mounting data

Height	88 mm
Width	116 mm
Depth	72 mm

Environmental characteristics | Climatic

Ambient temperature (storage, transport)	-40 °C ... 70 °C
--	------------------

Fuse

Operating voltage AC	250 V
Operating voltage DC	32 V
Nominal current	3 A
Protector type	OC - Overcurrent type
UL Use group	A
Terminals (UL 1077)	0
Tripping current (UL 1077)	1
Overload rating (UL 1077)	1
Short-circuit current rating (UL 1077)	1.0 KA, U1
UL CCN	QVNU2
UL-Standard	UL 1077
CSA Class	3215-30
CSA-Standard	CSA C22.2 No. 144.1-16

USA

Connection	Screw terminals SK
No. of poles	PE
Connections per pole	2
Protection contact present	Yes
Connection cross section max.	6 mm ²
AWG number max.	10
Operating voltage AC	125 V
Operating current	15 A
UL CCN	KCXS, KCXS7
UL-Standard	UL 943
CSA-Standard	CSA C22.2 No. 144.1-16

RJ45

Family construction form	RJ45
Looking techniques	Snap-in connector
Cable category min.	Cat5e
Family type Back side	RJ45
Operating voltage AC max. (UL-listed)	30 V
Operating voltage DC max. (UL-listed)	42,4 V
Current operating max. (UL)	175 mA