

MODLINK MSDD DBL COMBI INSERT


USA 2XNEMA 5-15 GFCI + RJ45, without touch protection

Art.No.: 4000-68000-4180000
Weight: 0.143 kg
Country of origin: CN
Model designation: Fr.Modul-AB-125-15-GFCI-SC+RJ45+w/o TP

2× NEMA-GFCI 5-15 (screw terminals)
1× RJ45, 8-pole metal, CAT5e (female/female)

Link to Product

Illustration



Product may differ from Image



Header

Material short textFr.Modul-AB-125-15-GFCI-SC+RJ45+w/o TP

Commercial data

URL Webshop	https://shop.murrelektronik.com/4000-68000-4180000
GTIN	4048879843737
ECLASS-6.0	27189217
ECLASS-6.1	27189217
ECLASS-7.0	27189217
ECLASS-7.1	27189217
ECLASS-8.0	27189217
ECLASS-8.1	27189217
ECLASS-9.0	27182806
ECLASS-9.1	27189217
ECLASS-10.0.1	27182806
ECLASS-10.1	27182806
ECLASS-11.0	27182806
ECLASS-11.1	27182806
ECLASS-12.0	27182806
ECLASS-13.0	27182806
ECLASS-14.0	27182806

ETIM-5.0	EC000020
ETIM-6.0	EC000020
ETIM-7.0	EC000020
ETIM-8.0	EC000020
customs tariff number	85366990
EAN	4048879843737
Packaging unit	1
customs tariff number	85366990
EAN	4048879843737
Packaging unit	1

Mechanical data | Mounting data

Height	88 mm
Width	116 mm
Depth	72 mm

Environmental characteristics | Climatic

Ambient temperature (storage, transport)	-40 °C
--	--------

USA

Connection	Screw terminals SK
No. of poles	PE
Connections per pole	2
Protection contact present	Yes
Connection cross section max.	6 mm ²
AWG number max.	10
Operating voltage AC	125 V
Operating current	15 A

RJ45

Family construction form	RJ45
Looking techniques	Snap-in connector
Cable category min.	Cat5e
Family type Back side	RJ45
Operating voltage AC max. (UL-listed)	30 V
Operating voltage DC max. (UL-listed)	42,4 V
Current operating max. (UL)	175 mA