


MODLINK MSDD DBL COMBI INSERT GREAT BRITAIN

- 1xUSB, 1xRJ45 fem./fem. + RCD opening
- Art.No.: 4000-68000-4320003
- Weight: 0.130 kg
- Country of origin: CZ
- Model designation: Fr.Modul-G-250-13-SC+RJ45+USB+RCD cutout
- 1× Great Britain (BS)
- 1× RJ45, 8-pole metal, CAT5e (female/female)
- 1× FI cut-out
- 1× USB 3.0 (female/female) form A

Link to Product

Illustration



Product may differ from Image



Header	
Material short text	Fr.Modul-G-250-13-SC+RJ45+USB+RCD cutout
Commercial data	
URL Webshop	https://shop.murrelektronik.com/4000-68000-4320003
GTIN	4048879547079
ECLASS-6.0	27189217
ECLASS-6.1	27189217
ECLASS-7.0	27189217
ECLASS-7.1	27189217
ECLASS-8.0	27189217
ECLASS-8.1	27189217
ECLASS-9.0	27182806
ECLASS-9.1	27189217
ECLASS-10.0.1	27182806
ECLASS-10.1	27182806
ECLASS-11.0	27182806
ECLASS-11.1	27182806
ECLASS-12.0	27182806

ECLASS-13.0	27182806
ECLASS-14.0	27182806
ETIM-5.0	EC000020
ETIM-6.0	EC000020
ETIM-7.0	EC000020
ETIM-8.0	EC000020
customs tariff number	85366990
EAN	4048879547079
Packaging unit	1

Mechanical data | Mounting data

Height	88 mm
Width	116 mm
Depth	70 mm

Environmental characteristics | Climatic

Ambient temperature (storage, transport)	5 °C
--	------

England

No. of poles	PE
Protection contact present	Yes
Operating voltage AC	250 V
Operating current	13 A

USB

USB specification	3.0
Looking techniques	Snap-in connector
Data transmission rate max.	5.000 Mbit/s
Operating voltage AC	48 V
Operating voltage DC	48 V
Operating current	1,5 A
Operating voltage AC max. (UL-listed)	30 V
Operating voltage DC max. (UL-listed)	42,4 V

RJ45

Family construction form	RJ45
Looking techniques	Snap-in connector
Cable category min.	Cat5e
Family type Back side	RJ45
Operating voltage AC max. (UL-listed)	30 V
Operating voltage DC max. (UL-listed)	42,4 V
Current operating max. (UL)	175 mA