

Murrelektronik GmbH | Grabenstraße 29 | 71570 Oppenweiler | Fon +49 (71 91) 47-0 | Fax +49 (71 91) 47-491000 | shop@murrelektronik.com | shop.murrelektronik.com

ECLASS-14.0	27182806
ETIM-5.0	EC002625
ETIM-6.0	EC002625
ETIM-7.0	EC002625
ETIM-8.0	EC002625
customs tariff number	85366990
EAN	4048879601009
Packaging unit	1

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP20
-------------------------------------	------

Mechanical data | Mounting data

Height	87,5 mm
Width	50,7 mm
Depth	43 mm

Environmental characteristics | Climatic

Operating temperature min.	-5 °C
Operating temperature max.	50 °C
Ambient temperature (storage, transport)	-10 °C ... 60 °C

Shielding plate

Connection information	Threaded hole M4
Tightening torque	0,9 Nm
Tightening torque tolerance	± 0,1 Nm

France (UTE-NF)

Connection	Screw terminals SK
No. of poles	PE
Connections per pole	2
Protection contact present	Yes
Connection cross section max.	4 mm ²
AWG number max.	12
Operating voltage AC	250 V
Operating current	16 A

RJ45

Family construction form	RJ45
Looking techniques	Snap-in connector
Cable category min.	Cat6a
Family type Back side	RJ45
Operating voltage AC max. (UL-listed)	30 V
Operating voltage DC max. (UL-listed)	42,4 V
Current operating max. (UL)	175 mA