

MODLINK MSDD SINGLE COMBI INSERT DANEMARK

2x data cutout

Art.No.: 4000-68000-4550000
Weight: 0.042 kg
Country of origin: DE
Model designation: Fr.Modul-CK-250-13-PT+2xdata cutout

1× Denmark (white)
2× RJ45 cut-out

Link to Product

Illustration



Product may differ from Image



Header

Material short textFr.Modul-CK-250-13-PT+2xdata cutout

Commercial data

URL Webshop	https://shop.murrelektronik.com/4000-68000-4550000
GTIN	4048879601085
ECLASS-6.0	27189217
ECLASS-6.1	27189217
ECLASS-7.0	27189217
ECLASS-7.1	27189217
ECLASS-8.0	27189217
ECLASS-8.1	27189217
ECLASS-9.0	27182806
ECLASS-9.1	27189217
ECLASS-10.0.1	27182806
ECLASS-10.1	27182806
ECLASS-11.0	27182806
ECLASS-11.1	27182806
ECLASS-12.0	27182806
ECLASS-13.0	27182806
ECLASS-14.0	27182806

ETIM-5.0	EC000020
ETIM-6.0	EC000020
ETIM-7.0	EC000020
ETIM-8.0	EC000020
customs tariff number	85366990
EAN	4048879601085
Packaging unit	1

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP20
-------------------------------------	------

Mechanical data | Mounting data

Height	87,5 mm
Width	50,7 mm
Depth	43 mm

Environmental characteristics | Climatic

Operating temperature min.	-5 °C
Operating temperature max.	50 °C
Ambient temperature (storage, transport)	-10 °C ... 60 °C

Shielding plate

Connection information	Threaded hole M4
Tightening torque	0,9 Nm
Tightening torque tolerance	± 0,1 Nm

Denmark

Connection	Spring clamp terminals FK
No. of poles	PE
Connections per pole	2
Protection contact present	Yes
Connection cross section max.	2,5 mm ²
AWG number max.	14
Operating voltage AC	250 V
Operating current	13 A