

Modlink MSDD-set:

Frame 4000-68113-0000000,
Art.No.: 4000-68113-3210000
Weight: 0.338 kg
Country of origin: CZ
Model designation: MSDD_1MV_INDIEEN_

Link to Product

Illustration



Product may differ from Image

Header	
Material short text	MSDD_1MV_INDIEEN_
Commercial data	
URL Webshop	https://shop.murrelektronik.com/4000-68113-3210000
GTIN	4048879382397
ECLASS-6.0	27189217
ECLASS-6.1	27189217
ECLASS-7.0	27189217
ECLASS-7.1	27189217
ECLASS-8.0	27189217
ECLASS-8.1	27189217
ECLASS-9.0	27182806

ECLASS-9.1	27189217
ECLASS-10.0.1	27182806
ECLASS-10.1	27182806
ECLASS-11.0	27182806
ECLASS-11.1	27182806
ECLASS-12.0	27182806
ECLASS-13.0	27182806
ECLASS-14.0	27182806
ETIM-5.0	EC002625
ETIM-6.0	EC002625
ETIM-7.0	EC002625
ETIM-8.0	EC002625
customs tariff number	85389099
EAN	4048879382397
Packaging unit	1
customs tariff number	85389099
EAN	4048879382397
Packaging unit	1

Frame

Material housing	Fine zinc die casting
Coating housing	surface finished
Suitable for installation wall thickness min.	1 mm
Suitable for installation wall thickness max.	5 mm
Degree of protection (EN IEC 60529)	IP65
Operating temperature min.	-10 °C
Operating temperature max.	60 °C
Storage temperature min.	-25 °C

India

Connection	Screw terminals SK
No. of poles	PE
Connections per pole	2
Protection contact present	Yes
Connection cross section max.	1,5 mm ²
AWG number max.	16
Operating voltage AC	240 V
Operating current	5 A