

Modlink MSDD-set: Frame 4000-68123-0000000,



insert 4000-68000-0040000 + 4000-68000-1210000


Art.No.: 4000-68123-0041210

Weight: 0.649 kg

Country of origin: CN

Model designation: MSDD_2MV_NEMA5-15SK_RJ45+BL_

[Link to Product](#)**Illustration**



Product may differ from Image

Header

Material short text MSDD_2MV_NEMA5-15SK_RJ45+BL_

Commercial data

URL Webshop <https://shop.murrelektronik.com/4000-68123-0041210>

GTIN 4048879034708

ECLASS-6.0 27189217

ECLASS-6.1 27189217

ECLASS-7.0 27189217

ECLASS-7.1 27189217

ECLASS-8.0 27189217

ECLASS-8.1 27189217

ECLASS-9.0 27182806

ECLASS-9.1 27189217

ECLASS-10.0.1 27182806

ECLASS-10.1 27182806

ECLASS-11.0 27182806

ECLASS-11.1 27182806

ECLASS-12.0 27182806

ECLASS-13.0 27182806

ECLASS-14.0 27182806

ETIM-5.0 EC002625

ETIM-6.0 EC002625

ETIM-7.0 EC002625

ETIM-8.0 EC002625

customs tariff number 85366990

EAN 4048879034708

Packaging unit 1

customs tariff number 85366990

EAN 4048879034708

Packaging unit 1

Frame

Material housing Fine zinc die casting

Coating housing surface finished

Suitable for installation wall thickness min. 1 mm

Suitable for installation wall thickness max. 5 mm

Degree of protection (EN IEC 60529) IP65

Operating temperature min. -10 °C

Operating temperature max.	60 °C
Storage temperature min.	-25 °C

USA

Connection	Screw terminals SK
No. of poles	PE
Connections per pole	2
Protection contact present	Yes
Connection cross section max.	2,5 mm ²
AWG number max.	14
Operating voltage AC	125 V
Operating current	15 A

RJ45

Family construction form	RJ45
Looking techniques	Snap-in connector
Cable category min.	Cat5e
Family type Back side	RJ45
Operating voltage AC max. (UL-listed)	30 V
Operating voltage DC max. (UL-listed)	42,4 V
Current operating max. (UL)	175 mA