

Modlink MSDD-set: Frame 4000-68123-0000000,


insert 4000-68000-1200000 + 4000-68000-0040000


Art.No.: 4000-68123-1200040

Weight: 0.655 kg

Country of origin: CN

Model designation: MSDD_2MV_2XRJ45_NEMA5-15SK_

[Link to Product](#)**Illustration**



Product may differ from Image

Header

Material short text MSDD_2MV_2XRJ45_NEMA5-15SK_

Commercial data

URL Webshop	https://shop.murrelektronik.com/4000-68123-1200040
GTIN	4048879375528
ECLASS-6.0	27189217
ECLASS-6.1	27189217
ECLASS-7.0	27189217
ECLASS-7.1	27189217
ECLASS-8.0	27189217
ECLASS-8.1	27189217
ECLASS-9.0	27182806
ECLASS-9.1	27189217
ECLASS-10.0.1	27182806
ECLASS-10.1	27182806
ECLASS-11.0	27182806
ECLASS-11.1	27182806
ECLASS-12.0	27182806
ECLASS-13.0	27182806
ECLASS-14.0	27182806
ETIM-5.0	EC002625
ETIM-6.0	EC002625
ETIM-7.0	EC002625
ETIM-8.0	EC002625
customs tariff number	85366990
EAN	4048879375528
Packaging unit	1

Frame

Material housing	Fine zinc die casting
Coating housing	surface finished
Suitable for installation wall thickness min.	1 mm
Suitable for installation wall thickness max.	5 mm
Degree of protection (EN IEC 60529)	IP65
Operating temperature min.	-10 °C
Operating temperature max.	60 °C
Storage temperature min.	-25 °C

Shielding plate

Connection information Threaded hole M4

Tightening torque	0,9 Nm
Tightening torque tolerance	± 0,1 Nm

USA

Connection	Screw terminals SK
No. of poles	PE
Connections per pole	2
Protection contact present	Yes
Connection cross section max.	2,5 mm ²
AWG number max.	14
Operating voltage AC	125 V
Operating current	15 A

RJ45

Family construction form	RJ45
Looking techniques	Snap-in connector
Cable category min.	Cat5e
Family type Back side	RJ45
Operating voltage AC max. (UL-listed)	30 V
Operating voltage DC max. (UL-listed)	42,4 V
Current operating max. (UL)	175 mA