

**Modlink MSDD-set: Frame 4000-68213-0000000,**


insert 4000-68000-0030000

Art.No.: 4000-68213-0030000

Weight: 0.202 kg

Country of origin: CZ

Model designation: MSDD\_1MVIK\_NEMA5-15L\_

**Link to Product****Illustration**

Product may differ from Image

**Header**

Material short text MSDD\_1MVIK\_NEMA5-15L\_

**Commercial data**

URL Webshop	<a href="https://shop.murrelektronik.com/4000-68213-0030000">https://shop.murrelektronik.com/4000-68213-0030000</a>
GTIN	4048879033534
ECLASS-6.0	27189217
ECLASS-6.1	27189217
ECLASS-7.0	27189217
ECLASS-7.1	27189217
ECLASS-8.0	27189217
ECLASS-8.1	27189217
ECLASS-9.0	27182806

ECLASS-9.1	27189217
ECLASS-10.0.1	27182806
ECLASS-10.1	27182806
ECLASS-11.0	27182806
ECLASS-11.1	27182806
ECLASS-12.0	27182806
ECLASS-13.0	27182806
ECLASS-14.0	27182806
ETIM-5.0	EC002625
ETIM-6.0	EC002625
ETIM-7.0	EC002625
ETIM-8.0	EC002625
customs tariff number	85389099
EAN	4048879033534
Packaging unit	1

**Frame**

Material housing	Fine zinc die casting
Material lid	PC
Coating housing	surface finished
Color cover	transparent
Suitable for installation wall thickness min.	1 mm
Suitable for installation wall thickness max.	5 mm
Degree of protection (EN IEC 60529)	IP65
Operating temperature min.	-10 °C
Operating temperature max.	60 °C
Storage temperature min.	-25 °C

**USA**

Connection	Plug-solder connection
No. of poles	PE
Protection contact present	Yes
Operating voltage AC	125 V
Operating current	15 A