

Modlink MSDD-set: Frame 4000-68223-0000000,


insert 4000-68000-3290000 + 4000-68000-1200000


Art.No.: 4000-68223-3291200

Weight: 0.470 kg

Country of origin: DE

Model designation: MSDD_2MVIPK_2xBrasilien_2XRJ45_

[Link to Product](#)**Illustration**



Product may differ from Image

Header

Material short text MSDD_2MVIPK_2xBrasilien_2XRJ45_

Commercial data

URL Webshop <https://shop.murrelektronik.com/4000-68223-3291200>

GTIN 4048879552240

ECLASS-6.0 27189217

ECLASS-6.1 27189217

ECLASS-7.0 27189217

ECLASS-7.1 27189217

ECLASS-8.0 27189217

ECLASS-8.1 27189217

ECLASS-9.0 27182806

ECLASS-9.1 27189217

ECLASS-10.0.1 27182806

ECLASS-10.1 27182806

ECLASS-11.0 27182806

ECLASS-11.1 27182806

ECLASS-12.0 27182806

ECLASS-13.0 27182806

ECLASS-14.0 27182806

ETIM-5.0 EC002625

ETIM-6.0 EC002625

ETIM-7.0 EC002625

ETIM-8.0 EC002625

customs tariff number 85366990

EAN 4048879552240

Packaging unit 1

customs tariff number 85366990

EAN 4048879552240

Packaging unit 1

Frame

Material housing Fine zinc die casting

Material lid PC

Coating housing surface finished

Color cover transparent

Suitable for installation wall thickness min. 1 mm

Suitable for installation wall thickness max. 5 mm

Degree of protection (EN IEC 60529)	IP65
Operating temperature min.	-10 °C
Operating temperature max.	60 °C
Storage temperature min.	-25 °C

Shielding plate

Connection information	Threaded hole M4
Tightening torque	0,9 Nm
Tightening torque tolerance	± 0,1 Nm

RJ45

Family construction form	RJ45
Looking techniques	Snap-in connector
Cable category min.	Cat5e
Family type Back side	RJ45
Operating voltage AC max. (UL-listed)	30 V
Operating voltage DC max. (UL-listed)	42,4 V
Current operating max. (UL)	175 mA