

MODLINK MSDD FRAME DBL GRAY

Closure Daimler

Art.No.: 4000-68524-0000003

Weight: 0.169 kg



Country of origin: DE

Model designation: Rahmenmodul 2-fach grau Daimler

Frame: plastic PA black

Lid: plastic, PBT gray

Closure: Daimler

[Link to Product](#)**Illustration**

Product may differ from Image

Header

Material short text Rahmenmodul 2-fach grau Daimler

Commercial data

URL Webshop	https://shop.murrelektronik.com/4000-68524-0000003
GTIN	4048879388757
ECLASS-6.0	27144001
ECLASS-6.1	27189260
ECLASS-7.0	27189260

ECLASS-7.1	27189260
ECLASS-8.0	27189260
ECLASS-8.1	27189260
ECLASS-9.0	27182810
ECLASS-9.1	27189260
ECLASS-10.0.1	27182810
ECLASS-10.1	27182810
ECLASS-11.0	27182810
ECLASS-11.1	27182810
ECLASS-12.0	27182810
ECLASS-13.0	27182810
ECLASS-14.0	27182810
ETIM-5.0	EC002625
ETIM-6.0	EC002625
ETIM-7.0	EC002625
ETIM-8.0	EC002625
customs tariff number	85389099
EAN	4048879388757
Packaging unit	1

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP65
-------------------------------------	------

Mechanical data | Material data

Material housing	PA
Color housing	black
Material lid	PBT
Color cover	gray

Mechanical data | Mounting data

Height	127 mm
Width	131 mm
Depth	43 mm
Suitable for installation wall thickness min.	1 mm
Suitable for installation wall thickness max.	5 mm

Environmental characteristics | Climatic

Operating temperature min.	-30 °C
Operating temperature max.	70 °C
Ambient temperature (storage, transport)	-30 °C ... 80 °C

Frame

Material housing	PA
Color housing	black
Material lid	PBT
Color cover	gray
Suitable for installation wall thickness min.	1 mm
Suitable for installation wall thickness max.	5 mm
Degree of protection (EN IEC 60529)	IP65
Operating temperature min.	-30 °C
Operating temperature max.	70 °C
Storage temperature min.	-30 °C