

## MODLINK MSDD CABLE ENTRY SYSTEM

KDP/R

Art.No.: 4000-70703-0500080

Weight: 0.040 kg

Country of origin: DE

Model designation: KDP/R M50/8

round (M50)

For sale only in packing units

Cable diameter (7) x 3...6.5 mm, (1) x 6...10 mm

[Link to Product](#)

Illustration



Product may differ from Image

### Header

Material short text KDP/R M50/8

### Commercial data

URL Webshop	<a href="https://shop.murrelektronik.com/4000-70703-0500080">https://shop.murrelektronik.com/4000-70703-0500080</a>
GTIN	4048879031615
ECLASS-6.0	27189217
ECLASS-6.1	27400604
ECLASS-7.0	27400604
ECLASS-7.1	27400604
ECLASS-8.0	27400604
ECLASS-8.1	27400604
ECLASS-9.0	27400604
ECLASS-9.1	27400604
ECLASS-10.0.1	27400604
ECLASS-10.1	27400604
ECLASS-11.0	27400604
ECLASS-11.1	27400604
ECLASS-12.0	27400604
ECLASS-13.0	27400604
ECLASS-14.0	27400604
ETIM-5.0	EC000211
ETIM-6.0	EC000211
ETIM-7.0	EC000211

ETIM-8.0	EC000211
customs tariff number	39269097
EAN	4048879031615
Packaging unit	1

**Device protection | Electrical**

Degree of protection (EN IEC 60529)	IP65
-------------------------------------	------

**Mechanical data | Material data**

Material housing	PA
------------------	----

**Mechanical data | Mounting data**

Height	33 mm
Width	58 mm
Depth	58 mm
Mounting method	geschnappt, screwed
Sheet thickness min. (screw mounting)	1,5 mm
Sheet thickness max. (screw mounting)	2 mm
Sheet thickness min. (snap-on mounting)	1,5 mm
Sheet thickness max. (snap-on mounting)	2 mm

**Environmental characteristics | Climatic**

Operating temperature min.	-30 °C
Operating temperature max.	70 °C