

MODLINK MSDD CABLE ENTRY SYSTEM

KDP/R

Art.No.: 4000-70703-0630080
Weight: 0.054 kg
Country of origin: DE
Model designation: KDP/R M63/8

round (M63)
For sale only in packing units
Cable diameter (2)× 3...6.5 mm, (4)× 5...9.2 mm, (2)× 9.6...15.9 mm

Link to Product

Illustration



Product may differ from Image

Header	
Material short text	KDP/R M63/8
Commercial data	
URL Webshop	https://shop.murrelektronik.com/4000-70703-0630080
GTIN	4048879031608
ECLASS-6.0	27189217
ECLASS-6.1	27400604
ECLASS-7.0	27400604
ECLASS-7.1	27400604
ECLASS-8.0	27400604
ECLASS-8.1	27400604
ECLASS-9.0	27400604
ECLASS-9.1	27400604
ECLASS-10.0.1	27400604
ECLASS-10.1	27400604
ECLASS-11.0	27400604
ECLASS-11.1	27400604
ECLASS-12.0	27400604
ECLASS-13.0	27400604
ECLASS-14.0	27400604
ETIM-5.0	EC000211
ETIM-6.0	EC000211
ETIM-7.0	EC000211

ETIM-8.0	EC000211
customs tariff number	39269097
EAN	4048879031608
Packaging unit	1
Device protection Electrical	
Degree of protection (EN IEC 60529)	IP65
Mechanical data Material data	
Material housing	PA
Mechanical data Mounting data	
Height	34 mm
Width	71 mm
Depth	71 mm
Mounting method	geschnappt, screwed
Sheet thickness min. (screw mounting)	1.5 mm
Sheet thickness max. (screw mounting)	2 mm
Sheet thickness min. (snap-on mounting)	1.5 mm
Sheet thickness max. (snap-on mounting)	2 mm
Environmental characteristics Climatic	
Operating temperature min.	-30 °C
Operating temperature max.	70 °C