

MODLINK MSDD CABLE ENTRY SYSTEM

KDP/R

Art.No.: 4000-70703-0630130

Weight: 0.058 kg

Country of origin: DE

Model designation: KDP/R M63/13

round (M63)

For sale only in packing units

Cable diameter (6) x 3...5.5 mm, (6) x 3...6.5 mm, (1) x 6...10 mm

Link to Product

Illustration



Product may differ from Image

Header

Material short text KDP/R M63/13

Commercial data

URL Webshop	https://shop.murrelektronik.com/4000-70703-0630130
GTIN	4048879031592
ECLASS-6.0	27189217
ECLASS-6.1	27400604
ECLASS-7.0	27400604
ECLASS-7.1	27400604
ECLASS-8.0	27400604
ECLASS-8.1	27400604
ECLASS-9.0	27400604
ECLASS-9.1	27400604
ECLASS-10.0.1	27400604
ECLASS-10.1	27400604
ECLASS-11.0	27400604
ECLASS-11.1	27400604
ECLASS-12.0	27400604
ECLASS-13.0	27400604
ECLASS-14.0	27400604
ETIM-5.0	EC000211
ETIM-6.0	EC000211
ETIM-7.0	EC000211

ETIM-8.0	EC000211
customs tariff number	39269097
EAN	4048879031592
Packaging unit	1

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP65
-------------------------------------	------

Mechanical data | Material data

Material housing	PA
------------------	----

Mechanical data | Mounting data

Height	34 mm
Width	71 mm
Depth	71 mm
Mounting method	geschnappt, screwed
Sheet thickness min. (screw mounting)	1.5 mm
Sheet thickness max. (screw mounting)	2 mm
Sheet thickness min. (snap-on mounting)	1.5 mm
Sheet thickness max. (snap-on mounting)	2 mm

Environmental characteristics | Climatic

Operating temperature min.	-30 °C
Operating temperature max.	70 °C