

MODLINK MSDD CABLE ENTRY SYSTEM

KDP/R KGM, Counter nut round M50/1,5

Art.No.: 4000-70704-0500000

Weight: 0.009 kg

Country of origin: DE

Model designation: KGM M50/1,5

[Link to Product](#)

Commercial data	
ECLASS-6.0	27149109
ECLASS-6.1	27149109
ECLASS-7.0	27069219
ECLASS-8.0	27069219
ECLASS-9.0	27140801
ECLASS-10.1	27144424
ECLASS-11.1	27144424
ECLASS-12.0	27140801
ETIM-5.0	EC000211
ETIM-6.0	EC000211
ETIM-7.0	EC000211
ETIM-8.0	EC000211
customs tariff number	39269097
customs tariff number	39269097
customs tariff number	39269097
EAN	4048879031578
EAN	4048879031578
EAN	4048879031578
Packaging unit	1
Packaging unit	1
Packaging unit	1
Device protection Electrical	
Degree of protection (EN IEC 60529)	IP65
Mechanical data Material data	
Material housing	PA
Mechanical data Mounting data	
Mounting method	screwed, geschnappt
Sheet thickness min. (snap-on mounting)	1,5 mm
Sheet thickness max. (snap-on mounting)	2 mm
Sheet thickness min. (screw mounting)	1,5 mm
Sheet thickness max. (screw mounting)	2 mm
Height	8 mm
Width	60 mm
Depth	60 mm
Environmental characteristics Climatic	
Operating temperature min.	-30 °C
Operating temperature max.	70 °C