

MSDD pass-through USB 3.0 form A, 0.6 m cable, design silver

Art.No.: 4000-73000-0150000




Weight: 0.059 kg


Country of origin: CZ

Model designation: MSDD PT22-S USB3.0 A/A F/M_0.6

Pass-through

1x USB 3.0 (female/male/0.6 m cable) form A

[Link to Product](#)
Illustration




Product may differ from Image



Header

Material short text MSDD PT22-S USB3.0 A/A F/M_0.6

Commercial data

URL Webshop	https://shop.murrelektronik.com/4000-73000-0150000
GTIN	4048879432894
ECLASS-6.0	27143423
ECLASS-6.1	27143419
ECLASS-7.0	27440515
ECLASS-7.1	27440515
ECLASS-8.0	27440515
ECLASS-8.1	27440515
ECLASS-9.0	27440515
ECLASS-9.1	27440515
ECLASS-10.0.1	27440515
ECLASS-10.1	27440515
ECLASS-11.0	27440515
ECLASS-11.1	27440515
ECLASS-12.0	27440515
ECLASS-13.0	27440515
ECLASS-14.0	27440515
ETIM-5.0	EC002625
ETIM-6.0	EC002625
ETIM-7.0	EC002625
ETIM-8.0	EC002625
customs tariff number	85444290
EAN	4048879432894
Packaging unit	1

Electrical data | Supply

Operating voltage AC	5 V
Operating voltage DC	5 V
Operating current max.	900 mA

Industrial Communication

Data transmission rate max.	5.000 Mbit/s
USB specification	3.0
Device protection	
Shielded	Yes
Device protection Electrical	
Degree of protection (EN IEC 60529)	IP20, IP65
Protection NEMA	12, 3R, 4x, 4, 13, 2
Additional condition protection degree	in closed state, inserted
Device protection Mechanical	
Mechanical endurance	1.500 cycles
Mechanical data Mounting data	
Depth	30 mm
Diameter	29,5 mm
Mounting depth	70 mm
Diameter cutout	22,5 mm
Approvals	
UL 50E	Yes