

## Modlight Illumix Xtreme Line 27W

LED machine lamp, IP69K, 24VDC, M12 connection

Art.No.: 4000-75827-1315000

Weight: 2.243 kg

Country of origin: AT

Model designation: Modlight Illumix Xtreme Line 27W

### [Link to Product](#)

#### Illustration



Product may differ from Image



#### Header

Material short text

Modlight Illumix Xtreme Line 27W

#### Commercial data

URL Webshop	<a href="https://shop.murrelektronik.com/4000-75827-1315000">https://shop.murrelektronik.com/4000-75827-1315000</a>
GTIN	4048879439169
ECLASS-6.0	27110303
ECLASS-6.1	27110390
ECLASS-7.0	27110390
ECLASS-7.1	27110390
ECLASS-8.0	27110390
ECLASS-8.1	27110390
ECLASS-9.0	27110345
ECLASS-9.1	27110345
ECLASS-10.0.1	27110345
ECLASS-10.1	27110345
ECLASS-11.0	27110345
ECLASS-11.1	27110345
ECLASS-12.0	27110345
ECLASS-13.0	27110345
ECLASS-14.0	27110345
ETIM-5.0	EC001334
ETIM-6.0	EC001334

ETIM-7.0	EC001334
ETIM-8.0	EC001334
customs tariff number	94054239
EAN	4048879439169
Packaging unit	1

#### Electrical data | Supply

Operating voltage DC	24 V
Current consumption max.	1.120 mA

#### HMI | Illumination properties

Illumination level	860 lx
--------------------	--------

#### Installation | Connection

Family construction form	M12
--------------------------	-----

#### Installation | Pin assignment

No. of poles	5
--------------	---

#### Device protection | Electrical

Degree of protection (ISO 20653:2013)	IP69K
Additional condition protection degree	inserted, screwed

#### Mechanical data | Material data

Material housing	Aluminum
Housing properties	with stainless steel cover

#### Mechanical data | Mounting data

Height	43 mm
Width	97 mm
Depth	441 mm

#### Environmental characteristics | Climatic

Operating temperature min.	-20 °C
Operating temperature max.	55 °C