

Murrelektronik Inc. | 1327 Northbrook Parkway, Suite 460 | Suwanee, GA 30024 | Fon +1 770 497-9292 | Fax +1 770 497-9391 | shop@murrinc.com | shop.murrinc.com

ETIM-5.0	EC001152
ETIM-6.0	EC001152
ETIM-7.0	EC001152
ETIM-8.0	EC001152
customs tariff number	85319000
EAN	4048879751513
Packaging unit	1

Electrical data | Supply

Operating voltage DC	24 V
Operating voltage DC min.	21,6 V
Operating voltage DC max.	26,4 V

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP65
Additional condition protection degree	locked, inserted

Mechanical data | Material data

Material housing	Plastic
Color housing	black

Mechanical data | Mounting data

Height	180 mm
Width	50 mm
Depth	50 mm

Environmental characteristics | Climatic

Operating temperature min.	-30 °C
Operating temperature max.	60 °C

Connection type 1

Family construction form	terminal
No. of poles	9
Gender	female
Connection	Spring clamp terminals FK
PIN 1	LED-Modul RD
PIN 2	LED-Modul YE
PIN 3	LED-Modul GN
PIN 4	LED-Modul BU
PIN 5	LED-Modul CL
PIN 6	Buzzer
PIN 7	24 V DC (0 V)
PIN 8	Blinking
PIN 9	0 V (24 V DC)