

COMLIGHT56 LED BLUE STATUS LIGHT

Input 24VDC

Art.No.: 4000-76056-1114000

Weight: 0.060 kg

Country of origin: ID

Model designation: Comlight56-LED-B

Compact status light
blue**[Link to Product](#)****Illustration**

Product may differ from Image

**Header**

Material short text Comlight56-LED-B

Commercial data

URL Webshop	https://shop.murrelektronik.com/4000-76056-1114000
GTIN	4048879853873
ECLASS-6.0	27371220
ECLASS-6.1	27110390
ECLASS-7.0	27110390
ECLASS-7.1	27110390
ECLASS-8.0	27110390
ECLASS-8.1	27110390
ECLASS-9.0	27110350
ECLASS-9.1	27110345
ECLASS-10.0.1	27110345
ECLASS-10.1	27110350
ECLASS-11.0	27110345
ECLASS-11.1	27110350
ECLASS-12.0	27110350
ECLASS-13.0	27110345
ECLASS-14.0	27110345

ETIM-5.0	EC000232
ETIM-6.0	EC000232
ETIM-7.0	EC000232
ETIM-8.0	EC000232
customs tariff number	85319000
EAN	4048879853873
Packaging unit	1

Electrical data | Supply

Operating voltage DC	24 V
Current consumption max.	26 mA

HMI | Illumination properties

Luminous intensity	239 mcd
--------------------	---------

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP65
Additional condition protection degree	locked, inserted

Mechanical data | Material data

Material housing	Plastic
------------------	---------

Mechanical data | Mounting data

Height	61 mm
Width	56 mm
Depth	56 mm

Environmental characteristics | Climatic

Operating temperature min.	-30 °C
Operating temperature max.	50 °C

Connection type 1

Family construction form	terminal
No. of poles	2
Gender	female
Connection	Spring clamp terminals FK
PIN 1	24 V DC (0 V)
PIN 2	0 V (24 V DC)