

COMLIGHT56 LED BLUE STATUS LIGHT

With 4 pole M12 bottom exit

Art.No.: 4000-76056-1314000

Country of origin: CZ

Model designation: Comlight56-LED-B M12-U

Compact status light

Flange M12 male, 4-pole

blue

Link to Product

Illustration



Product may differ from Image



Header

Material short text Comlight56-LED-B M12-U

Commercial data

URL Webshop	https://shop.murrelektronik.com/4000-76056-1314000
GTIN	4048879855730
ECLASS-6.0	27371220
ECLASS-6.1	27110390
ECLASS-7.0	27110390
ECLASS-7.1	27110390
ECLASS-8.0	27110390
ECLASS-8.1	27110390
ECLASS-9.0	27110350
ECLASS-9.1	27110345
ECLASS-10.0.1	27110345
ECLASS-10.1	27110350
ECLASS-11.0	27110345
ECLASS-11.1	27110350
ECLASS-12.0	27110350
ECLASS-13.0	27110345
ECLASS-14.0	27110345

ETIM-5.0	EC000232
ETIM-6.0	EC000232
ETIM-7.0	EC000232
ETIM-8.0	EC000232
customs tariff number	85319000
EAN	4048879855730
Packaging unit	1

Electrical data | Supply

Operating voltage DC	24 V
Current consumption max.	26 mA

HMI | Illumination properties

Luminous intensity	239 mcd
--------------------	---------

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP65
Additional condition protection degree	locked, inserted

Mechanical data | Material data

Material housing	Plastic
------------------	---------

Mechanical data | Mounting data

Height	78,8 mm
Width	56 mm
Depth	56 mm

Environmental characteristics | Climatic

Operating temperature min.	-30 °C
Operating temperature max.	50 °C

Connection type 1

Family construction form	M12
No. of poles	4
Coding	A
Gender	male
PIN 3	BU 0 V (24 V DC)
PIN 4	BK 24 V DC (0 V)