

## COMLIGHT56 LED CLEAR STATUS LIGHT

With 4 pole M12 bottom exit

Art.No.: 4000-76056-1315000

Weight: 0.070 kg

Country of origin: CZ

Model designation: Comlight56-LED-C M12-U

Compact status light

Flange M12 male, 4-pole

clear

### [Link to Product](#)

#### Illustration



Product may differ from Image



#### Header

Material short text Comlight56-LED-C M12-U

#### Commercial data

URL Webshop	<a href="https://shop.murrelektronik.com/4000-76056-1315000">https://shop.murrelektronik.com/4000-76056-1315000</a>
GTIN	4048879855747
ECLASS-6.0	27371220
ECLASS-6.1	27110390
ECLASS-7.0	27110390
ECLASS-7.1	27110390
ECLASS-8.0	27110390
ECLASS-8.1	27110390
ECLASS-9.0	27110350
ECLASS-9.1	27110345
ECLASS-10.0.1	27110345
ECLASS-10.1	27110350
ECLASS-11.0	27110345
ECLASS-11.1	27110350
ECLASS-12.0	27110350
ECLASS-13.0	27110345

ECLASS-14.0	27110345
ETIM-5.0	EC000232
ETIM-6.0	EC000232
ETIM-7.0	EC000232
ETIM-8.0	EC000232
customs tariff number	85319000
EAN	4048879855747
Packaging unit	1

**Electrical data | Supply**

Operating voltage DC	24 V
Current consumption max.	26 mA

**HMI | Illumination properties**

Luminous intensity	1.541 mcd
--------------------	-----------

**Device protection | Electrical**

Degree of protection (EN IEC 60529)	IP65
Additional condition protection degree	locked, inserted

**Mechanical data | Material data**

Material housing	Plastic
------------------	---------

**Mechanical data | Mounting data**

Height	78,8 mm
Width	56 mm
Depth	56 mm

**Environmental characteristics | Climatic**

Operating temperature min.	-30 °C
Operating temperature max.	50 °C

**Connection type 1**

Family construction form	M12
No. of poles	4
Coding	A
Gender	male
PIN 3	BU 0 V (24 V DC)
PIN 4	BK 24 V DC (0 V)