

Modlight70 Pro LED modul green

Input 24VDC
Art.No.: 4000-76070-1013000
Weight: 0.065 kg
Country of origin: ID
Model designation: Modlight70 Pro LED-G
LED module (green)

Link to Product

Illustration



Product may differ from Image



Header	
Material short text	Modlight70 Pro LED-G
Commercial data	
URL Webshop	https://shop.murrelektronik.com/4000-76070-1013000
GTIN	4048879752640
ECLASS-6.0	27371200
ECLASS-6.1	27371220
ECLASS-7.0	27371220
ECLASS-7.1	27371220
ECLASS-8.0	27371220
ECLASS-8.1	27371220
ECLASS-9.0	27371220
ECLASS-9.1	27371220
ECLASS-10.0.1	27371220
ECLASS-10.1	27371220
ECLASS-11.0	27371220
ECLASS-11.1	27371220
ECLASS-12.0	27371220
ECLASS-13.0	27371220
ECLASS-14.0	27371220
ETIM-5.0	EC000232

ETIM-6.0	EC000232
ETIM-7.0	EC000232
ETIM-8.0	EC000232
customs tariff number	85319000
EAN	4048879752640
Packaging unit	1
Electrical data Supply	
Operating voltage DC	24 V
Operating voltage DC min.	21,6 V
Operating voltage DC max.	26,4 V
Current consumption max.	62,5 mA
Device protection Electrical	
Degree of protection (EN IEC 60529)	IP65
Additional condition protection degree	locked, inserted
Mechanical data Material data	
Material housing	PC
Mechanical data Mounting data	
Height	49 mm
Width	70 mm
Depth	70 mm
Environmental characteristics Climatic	
Operating temperature min.	-30 °C
Operating temperature max.	60 °C