

ETIM-7.0	EC001283
ETIM-8.0	EC001283
customs tariff number	85369010
EAN	4048879049429
Packaging unit	1

Electrical data | Supply

Operating voltage AC max.	30 V
Operating voltage DC max.	30 V
Total current max.	20 A

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP20
-------------------------------------	------

Mechanical data | Mounting data

Height	70 mm
Width	56 mm
Depth	32,5 mm

Environmental characteristics | Climatic

Operating temperature min.	0 °C
Operating temperature max.	55 °C
Ambient temperature (storage, transport)	-40 °C ... 85 °C

Connection type 4

Family construction form	terminal
No. of poles	1
Gender	female
Color contact carrier	green
Connection	Spring clamp terminals FK
PIN 1	00
Family construction form	terminal
No. of poles	1
Gender	female
Color contact carrier	green
Connection	Spring clamp terminals FK
PIN 1	01
Family construction form	terminal
No. of poles	7
Gender	female
Color contact carrier	black
Connection	Spring clamp terminals FK
PIN 1	00
PIN 2	01
PIN 3	02
PIN 4	03
PIN 5	04
PIN 6	05
PIN 7	06
Family construction form	terminal
No. of poles	7
Gender	female
Color contact carrier	black
Connection	Spring clamp terminals FK
PIN 1	07
PIN 2	08
PIN 3	09

PIN 4	10
PIN 5	11
PIN 6	12
PIN 7	13