

EOL - MKDP 24/14 Cable entry plate

Product discontinued

Art.No.: 7000-90201-2414000

Weight: 0.101 kg

Country of origin: DE

Model designation: MKDP 24/14

Size 24

Cable diameter (6)× 3...6.5 mm, (4)× 5...9.2 mm, (4)× 9.6...15.9 mm

[Link to Product](#)**Illustration**

Product may differ from Image

Commercial data

ECLASS-6.0	27279221
ECLASS-6.1	27260702
ECLASS-7.0	27440102
ECLASS-8.0	27440102
ECLASS-9.0	27440116
ECLASS-10.1	27440106
ECLASS-11.1	27440106
ECLASS-12.0	27440116
ETIM-5.0	EC001855
customs tariff number	39269097
customs tariff number	39269097
EAN	4048879568548
EAN	4048879568548
Packaging unit	1
Packaging unit	1

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP66
-------------------------------------	------

Mechanical data | Material data

Material housing	PA
Combustibility class (UL94)	V-0
Material gasket	TPE

Mechanical data | Mounting data

Height	147,5 mm
--------	----------

Width	59,5 mm
-------	---------

Depth	25 mm
-------	-------

Environmental characteristics | Climatic

Operating temperature min.	-30 °C
----------------------------	--------

Operating temperature max.	100 °C
----------------------------	--------