

**EXACT8, 4XM8, 3 POLE**

Conn. M12 8 pole

Art.No.: 8000-84070-0000000

Weight: 0.082

Country of origin: DE

Model designation: MVP8N-NS4D




4-way, 3-pole


M12 (8-pole)

Inline face or side mounting

Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request.

[Link to Product](#)
**Illustration**




Product may differ from Image



#### Header

Material short text MVP8N-NS4D

#### Commercial data

URL Webshop	<a href="https://shop.murrelektronik.com/8000-84070-0000000">https://shop.murrelektronik.com/8000-84070-0000000</a>
GTIN	4048879056304
ECLASS-6.0	27279219
ECLASS-6.1	27279219
ECLASS-7.0	27279219
ECLASS-7.1	27279219
ECLASS-8.0	27279219
ECLASS-8.1	27279219
ECLASS-9.0	27440111
ECLASS-10.0.1	27440111
ECLASS-10.1	27440111
ECLASS-11.0	27440111
ECLASS-11.1	27440111
ECLASS-12.0	27440111
ECLASS-13.0	27440111
ECLASS-14.0	27440111
ETIM-5.0	EC002585
ETIM-6.0	EC002585
ETIM-7.0	EC002585
ETIM-8.0	EC002585
customs tariff number	85366990
EAN	4048879056304
Packaging unit	1

#### Electrical data | Supply

Operating voltage DC 24 V

Current operating per contact max. 2 A

#### Device protection | Electrical

Degree of protection (EN IEC 60529) IP67, IP65

#### Device protection | Media

