


Modlink MSDD-set: Frame 4000-68112-0000000,

insert 4000-68000-0510000

Art.No.: 4000-68112-0510000
Weight: 0.323 kg
Country of origin: DE
Model designation: MSDD_1SW_2X15BU_

Link to Product

Illustration



Product may differ from Image



Commercial data	
URL Webshop	https://shop.murrelektronik.com/4000-68112-0510000
GTIN	4048879036535
EU-Customs tariff number	85366990
US-Customs tariff number	8536694020
ECLASS-6.0	27189217
ECLASS-6.1	27189217
ECLASS-7.0	27189217

ECLASS-7.1	27189217
ECLASS-8.0	27189217
ECLASS-8.1	27189217
ECLASS-9.0	27189217
ECLASS-9.1	27189217
ECLASS-10.0.1	27182806
ECLASS-10.1	27182806
ECLASS-11.0	27182806
ECLASS-11.1	27182806
ECLASS-12.0	27182806
ECLASS-13.0	27182806
ECLASS-14.0	27182806
ETIM-5.0	EC002625
ETIM-6.0	EC002625
ETIM-7.0	EC002625
ETIM-8.0	EC002625
ETIM-9.0	EC002625
ETIM-10.0	EC002625
customs tariff number	85366990
EAN	4048879036535
Packaging unit	1

Frame

housing	Fine zinc die casting
Coating housing	KTL
Suitable for installation wall thickness min.	1 mm
Suitable for installation wall thickness max.	5 mm
Degree of protection (EN IEC 60529)	IP65
Operating temperature min.	-10 °C
Operating temperature max.	60 °C
Storage temperature min.	-25 °C

SUB-D15

Family construction form	SUB-D15
Gender	female
No. of poles	15
Looking techniques	Standard UNC 4-40 screw thread bolt (EN 60807)
Family type Back side	SUB-D15
Gender Rear	Solder connection
Operating voltage AC max. (UL-listed)	30 V
Operating voltage DC max. (UL-listed)	42,4 V
Current operating max. (UL)	175 mA