



Xenterra 8TX unmanaged Switch 8 Port 1000Mbit wall mounting

Art.No.: 58909
Weight: 0.260 kg
Country of origin: DE
Model designation: Xenterra 8TX GE WM

8 Port Unamanged IP20 Gigabit Switch
Wall mounting

Link to Product

Illustration



Product may differ from Image



Commercial data	
URL Webshop	https://shop.murrelektronik.com/58909
GTIN	4048879873550
Customs tariff number	85176200
ECLASS-6.1	19170106
ECLASS-7.0	19170106
ECLASS-7.1	19170106

ECLASS-8.0	19170106
ECLASS-8.1	19170106
ECLASS-9.0	19170106
ECLASS-9.1	19170106
ECLASS-10.0.1	19170402
ECLASS-10.1	19170402
ECLASS-11.0	19170402
ECLASS-11.1	19170402
ECLASS-12.0	19170402
ECLASS-13.0	19170402
ECLASS-14.0	19170402
customs tariff number	85176200
EAN	4048879873550
Packaging unit	1

Electrical data | Supply

Operating voltage AC min.	8 V
Operating voltage AC max.	28 V
Operating voltage DC min.	9 V
Operating voltage DC max.	36 V

Industrial Communication

Data transmission rate max.	1.000 Mbit/s
-----------------------------	--------------

Industrial communication | Ethernet functionality

VLAN unmanaged (IEEE 802.1Q)	Yes
Switch type	unmanaged
duplex	Full duplex
Auto-negotiation	Yes
Auto-crossover	Yes

Diagnostics

Alarm contact	No
Diagnostic	No voltage
LED display	Ethernet connection/data traffic

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP20
-------------------------------------	------

Mechanical data | Material data

housing	Metal
Color housing	black

Mechanical data | Mounting data

Height	105 mm
Width	85 mm
Depth	28 mm
Mounting method	screwed
Suitable for mounting type	Keyhole mounting

Environmental characteristics | Climatic

Operating temperature min.	-40 °C
Operating temperature max.	70 °C
Ambient temperature (storage, transport)	-40 °C ... 85 °C

Connection type 1

Connection type 1	8
Family construction form	RJ45
No. of poles	8
Gender	female

Color contact carrier	black
PIN 1	TD +
PIN 2	TD -
PIN 3	RD +
PIN 4	n.c.
PIN 5	n.c.
PIN 6	RD -
PIN 7	n.c.
PIN 8	n.c.