Description

- EMC protection
- Corrosion-resistant
- Protection rating UL50E tested
- All-purpose due to high corrosion resistance and high environmental protection



General Characteristics

Series	ULTRA H-A 3
Version	Surface-mount base M20
Locking mechanism	Single lever
Cable entry	Straight
Thread	M20x1.5
Protection (DIN EN 60529)	IP 65 (latched)
Protection (NEMA 250, UL50E)	4, 4X, 12 (latched)
Temperature range	-40°C to +100°C, short-term up to +125°C
Holding screws for inserts included	Yes
Cable Gland included	No

Materials and Surfaces

Housing, base material	Zinc die-casting
Housing, surface	Nickel-plated
Lever	Stainless steel
Holding screws for inserts	Stainless steel
Gasket	NBR

Approvals


VDE-Approval, VDE-REG.-Nr.	B437
UL-Approval UL-E-File Number	E75770

Standards

Safety Standard	IEC 61984; UL 1977

We reserve all rights according to DIN ISO 16016.

Technical Drawing



Remark

Photographs are not to scale and do not represent detailed images of the respective products.

We reserve all rights according to DIN ISO 16016.