

22260131	DATA SHEET	
Valid from: 12.09.2019	AB-C4-M12FS-F0,34	

Product description

Sensor/Actuator connector, straight socket, 4-pos.,
M12, A-coded, fast connection system, metal knurl,
cable diameter max. 6 mm



General properties

Ambient temperature	-25 to +80 °C
Protection degree	IP 65 / IP 67
Number of contacts	4
Outer diameter, cable	3.5 – 6.0 mm
Termination type	insulation displacement connection (IDC)
Termination cross section, AWG	26 - 22
Termination cross section, mm ²	0.14 – 0.34

Mechanical properties

Mating cycles	100
Rewiring, same cross section	5 times
Tightening torque, locking nut	0.8 Nm

Electrical properties

Rated voltage	125 V
Contact resistance	≤ 5 mΩ
Insulation resistance	≥ 10 ⁷ MΩ
Proof voltage, contact-contact	≥ 1.4 kV
Proof voltage, contact-housing	≥ 1.4 kV
Rated current	4 A
Overvoltage category	II
Pollution degree	3

Materials

Contact carrier	PA
Contact carrier, Inflammability class in accordance with UL 94	V0
Contacts, base material	CuSn
Contacts, surface	Ni/Au
Locking nut	Die-cast zinc, Ni plated
Grip body	PA
Sealing	NBR


Standards

Product standard	M12-Connector acc. to DIN EN 61076-2-101
------------------	--


Creator: MANA2/PDP Released: IVSE1/PDP	Document: DB22260131EN Version: 05	Page 1 of 2
---	---------------------------------------	-------------

22260131	DATA SHEET	
Valid from: 12.09.2019	AB-C4-M12FS-F0,34	

Drawings



Pin assignment



Application range

Automation, industrial machinery and plant engineering

Note

Photographs are not true to scale and do not represent detailed images of the respective products.

Creator: MANA2/PDP Released: IVSE1/PDP	Document: DB22260131EN Version: 05	Page 2 of 2
---	---------------------------------------	-------------