

FLEXIMARK® Character holders PTEF / CAB

Pre-cutted FLEXIMARK® Character holders PTEF for marking cables with labels or character strips. For assembly with cable ties.

Info

PTEF 9,5-35 included in FLEXIMARK® sample bag (article no. M3251010)



Suitable for outdoor use



Good chemical resistance



Halogen-free



Acid-resistant



UV-resistant

Benefits

Cost-saving, as you save the time for cutting

PC labels LFL are adapted to be pushed into different sizes of character-holder

Additional protection against UV- radiation and diverse chemicals

Application range

Suitable for FLEXIMARK® Flexilabels LFL as well as for DYMO® industry tapes

For cable/conduit marking

Assembly with 2.6 mm cable ties or fasten with screws and rivets when using end caps

Included

PTEF: without cable ties

CAB: with cable ties (135x2,6mm)

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC002248

ETIM 5.0 Class-Description: Mounting for labelling material

Last Update (11.01.2026)

©2026 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

FLEXIMARK® Character holders PTEF / CAB

Classification ETIM 6:

ETIM 6.0 Class-ID: EC002248

ETIM 6.0 Class-Description: Mounting for labelling material

Material:

Halogen-free polyethylene

Temperature range:

-75°C up to +80°C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

FLEXIMARK® products are sold in packaging units. As example if you like to order 640 labels of LCK 32 you just need to order 1 PU instead of 640 single labels.

FLEXIMARK® Character holders PTFE / CAB

Article number	Article designation	A (mm)	B (mm)	C (mm)	D (mm)	Markers / PU	PU
Without cable ties							
83254974	FLEXIMARK® PTFE 6-35 TR	8.7	6	35	47	50	1
83254960	FLEXIMARK® PTFE 9.5-18 TR	12.2	9.5	18	30	50	1
83254961	FLEXIMARK® PTFE 9.5-28 TR	12.2	9.5	28	40	50	1
83254963	FLEXIMARK® PTFE 9.5-35 TR	12.2	9.5	35	47	50	1
83254962	FLEXIMARK® PTFE 9.5-38 TR	12.2	9.5	38	50	50	1
83254964	FLEXIMARK® PTFE 9.5-58 TR	12.2	9.5	58	70	50	1
83254965	FLEXIMARK® PTFE 9.5-70 TR	12.2	9.5	70	82	50	1
83254976	FLEXIMARK® PTFE 12-28 TR	14.8	12	28	40	50	1
83280006	FLEXIMARK® PTFE 12-18 TR	14.8	12	18	30	50	1
83254977	FLEXIMARK® PTFE 12-38 TR	14.8	12	38	50	50	1
83254978	FLEXIMARK® PTFE 12-58 TR	14.8	12	58	70	50	1
83254982	FLEXIMARK® PTFE 19-50 TR	21.7	19	50	62	50	1
With cable ties							
83259091	FLEXIMARK® CAB 6-35 TR	8.7	6	35	47	50	1
83259087	FLEXIMARK® CAB 9.5-18 TR	12.2	9.5	18	30	50	1
83259084	FLEXIMARK® CAB 9.5-28 TR	12.2	9.5	28	40	50	1
83259088	FLEXIMARK® CAB 9.5-35 TR	12.2	9.5	35	47	50	1
83259086	FLEXIMARK® CAB 9.5-58 TR	12.2	9.5	58	70	50	1
83259078	FLEXIMARK® CAB 12-18 TR	14.8	12	18	30	50	1
83259079	FLEXIMARK® CAB 12-28 TR	14.8	12	28	40	50	1

Last Update (11.01.2026)

©2026 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03_16

FLEXIMARK® Character holders PTFE / CAB

Article number	Article designation	A (mm)	B (mm)	C (mm)	D (mm)	Markers / PU	PU
83259080	FLEXIMARK® CAB 12-38 TR	14.8	12	38	50	50	1
83259081	FLEXIMARK® CAB 12-58 TR	14.8	12	58	70	50	1
83259070	FLEXIMARK® CAB 19-50 TR	21.7	19	50	62	50	1

Last Update (11.01.2026)

©2026 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03_16