

NICKEL PLATED BRASS ADAPTERS

PG, NPT & Metric Combinations



PG/ NPT Adapters



Part Number	Thread Type & Size Male to Female	Standard Pack Size
01112	PG-11 to NPT 1/2"	10
01312	PG-13 to NPT 1/2"	10
01612	PG-16 to NPT 1/2"	10
02112	PG-21 to NPT 1/2"	10
02134	PG-21 to NPT 3/4"	10
02910	PG-29 to NPT 1"	10
03614	PG-36 to NPT 1-1/4"	10

NPT/ PG Adapters



Part Number	Thread Type & Size Male to Female	Standard Pack Size
11211	NPT 1/2" - PG-11	10
11213	NPT 1/2" - PG-13	10
11216	NPT 1/2" - PG-16	10
13411	NPT 3/4" - PG-11	10
13413	NPT 3/4" - PG-13	10
13416	NPT 3/4" - PG-16	10
13421	NPT 3/4" - PG-21	10
11116	NPT 1" - PG-16	10

SKINDICHT® MA-M/ NPT Adapters



Connecting adapter with Metric outer threads and NPT inner threads.

Part Number	Thread Type & Size Male to Female	Standard Pack Size
54020100	M-16X1.5 to NPT 1/2"	50
54020110	M-20X1.5 to NPT 1/2"	50
54020120	M-25X1.5 to NPT 1/2"	25
54020130	M-25X1.5 to NPT 3/4"	25
54020140	M-32X1.5 to NPT 1/2"	25
54020152	M-32X1.5 to NPT 1"	25
54020153	M-40X1.5 to NPT 1 1/4"	10

SKINDICHT® MA-M/ PG Adapters



Connecting adapter with Metric outer threads and PG inner threads.

Part Number	Thread Type & Size Male to Female	Standard Pack Size
52104200	M-16X1.5 to PG-7	100
52104210	M-20X1.5 to PG-9	50
52104220	M-25X1.5 to PG-11	50
52104230	M-25X1.5 to PG-13	50
52104240	M-25X1.5 to PG-16	50
52104250	M-32X1.5 to PG-16	25
52104260	M-32X1.5 to PG-21	25
52104270	M-40X1.5 to PG-21	25
52104280	M-50X1.5 to PG-29	10
52104290	M-63X1.5 to PG-36	10
52104300	M-63X1.5 to PG-42	10

SKINDICHT® ZS-M/ PG Adapters



A hexagonal connector with Metric outer threads and PG inner threads.

Part Number	Thread Type & Size Male to Female	Width Across Flats inches	Thread Length inches	Standard Pack Size
52104330	M-12x1.5 to PG-7	0.55	0.20	100
52104340	M-16x1.5 to PG-9	0.71	0.20	100
52104010	M-16x1.5 to PG-11	0.79	0.20	100
52104360	M-20x1.5 to PG-11	0.87	0.24	100
52104370	M-20x1.5 to PG-13	0.87	0.24	100
52104380	M-20x1.5 to PG-16	0.94	0.24	50
52104400	M-25x1.5 to PG-21	1.18	0.28	50
52104410	M-32x1.5 to PG-29	1.57	0.31	25
52104420	M-40x1.5 to PG-36	1.97	0.31	10
52104430	M-50x1.5 to PG-42	2.24	0.35	10
52104440	M-63x1.5 to PG-48	2.60	0.39	10

