



Order instruction:


- Purchase only in lot sizes and a multiple of that see product table below




Angle brackets 30 + 40
Die-cast zinc




Angle bracket 40-1
Die-cast zinc



Angle bracket 40x80-1
Die-cast zinc



Angle bracket 50/60
Die-cast zinc



Angle bracket F-60x60
Die-cast zinc

Code No.	Type	lot sizes	Version	A	B	C	D	E	F	G	H	I	O	L	R
Cast angle bracket															
4004101	30	10, 20, 30... pcs	2 braces	6.5	18	29	5	–	10	15	5.2	–	4	–	–
4014101	40-1	10, 20, 30... pcs	1 brace	8.4	28	38	5	–	14	19	5.2	–	–	–	–
4014102	40	10, 20, 30... pcs	2 braces	8.4	28	38	5	–	14	19	5.2	–	–	–	–
4034101	40x80-1	10, 20, 30... pcs	1 brace	8.5	28	78	8	–	14	61	5.2	–	6	38	20
4024101	50/60	10, 20, 30... pcs	2 braces	8.5	44	58	8	–	14	41	5.2	–	6	–	18
4124101	F-60x60	10, 20, 30... pcs	2 braces	8.5	48	58	8	20	14	40	5.2	–	6	–	17

Fixing sets
Fixing sets:

The angle brackets can be screwed to the profile with the fixing sets.

Material: Galvanised steel

Further slot stone types can be found on page 84 - 93



Fixing set with slot stone -N- (slot stone is slid into the slot from the side)



Fixing set with slot stone -K- (slot stone can be inserted edge-first into the slot retrospectively)



Fixing set with slot stone -R- (slot stone can be inserted into the slot retrospectively and twisted into position)

Code No.	Type	lot sizes	Version
Fixing sets			
4004110	30	10, 20, 30... pcs	M6x12, slot stone -N-
4026208	40	10, 20, 30... pcs	M8x16, slot stone -N-
4026202	50-80 + 40x80x160	10, 20, 30... pcs	M8x18, slot stone -N-
4694110	100-160 (except 40x80x160)	10, 20, 30... pcs	M8x22, slot stone -N-
4004111	30	10, 20, 30... pcs	M6x12, slot stone -K-
4014111	40	10, 20, 30... pcs	M8x16, slot stone -K-
4024111	50-80 + 40x80x160	10, 20, 30... pcs	M8x18, slot stone -K-
4694111	100-160 (except 40x80x160)	10, 20, 30... pcs	M8x22, slot stone -K-
4004112	30	10, 20, 30... pcs	M6x12, slot stone -R-
4026209	40	10, 20, 30... pcs	M8x16, slot stone -R-
4026210	50-80 + 40x80x160	10, 20, 30... pcs	M8x18, slot stone -R-
4694112	100-160 (except 40x80x160)	10, 20, 30... pcs	M8x22, slot stone -R-