

GGM/GGM-V

Electronic/Glass Fuses

MIDGET, PC MOUNT & MINIATURE FUSES

GGM/GGM-V

- Glass body
- Fast-acting
- 5 mm x 20 mm
- 1-1/2" Axial leads optional

4/10A through 2A,
250VAC, UL Listed and
CSA Certified

8A, 125VAC, UL Listed
and CSA Certified



STANDARD FUSE AMPERE RATINGS

Catalog Number	Axial Lead Cat. No	Ampere Rating	Volts	I.R.
GGM4/10	GGM-V4/10	4/10A	250V	1
GGM6/10	GGM-V6/10	6/10A	250V	1
	GGM-V7/10	7/10A	250V	1
GGM8/10	GGM-V8/10	8/10A	250V	1
GGM1		1A	250V	1
GGM2		2A	250V	1
	GGM-V8	8A	125V	2

1. 250VAC @ 200A I.R./125VAC @ 10kA I.R.
2. 125VAC @ 10kA I.R.



© 2025 Mersen. All rights reserved. Mersen reserves the right to change, update, or correct, without notice, any information contained in this datasheet.