


**Product:** [1175A](#) 

T1/DS1 Central Office, #22-1pr, Shielded, CMR/CMG



## Product Description

22 AWG solid tinned copper conductors, twisted pairs, polyethylene insulation, overall Beldfoil® shield (100% coverage), 24 AWG solid tinned copper drain wire, PVC jacket.

## Technical Specifications

### Product Overview

Suitable Applications:	Bits Timing Cable, DS1, T1, Central Office, Cross-Connect, Interconnect
------------------------	---

### Construction Details

#### Conductor

Element	Size	Stranding	Material	No. of Pairs
Pair(s)	22 AWG	Solid	TC - Tinned Copper	1

#### Insulation

Element	Material	Nom. Insulation Diameter	Color Code
Pair(s)	PE - Polyethylene	0.073 in (1.9 mm)	Blue & White

#### Outer Shield

Shield Type	Material	Coverage	Drainwire Type
Tape	Bi-Laminate (Alum+Poly)	100%	24 AWG (Solid) TC

#### Outer Jacket

Material	Nom. Diameter	Ripcord
PVC - Polyvinyl Chloride	0.195 in	Yes

Overall Cable Diameter (Nominal): 0.195 in

### Electrical Characteristics

#### Electricals

Nom. Characteristic Impedance
100 Ohm

#### High Frequency

Frequency [MHz]
0.772
1
4
10
20

#### Voltage

UL Voltage Rating
300 V

### Mechanical Characteristics

## Temperature

UL Temperature	Operating
75°C	-20°C to +75°C

## Bend Radius

Stationary Min.	Installation Min.
1.95 in (49.5 mm)	1.95 in

Max. Pull Tension:	20.7 lbs (9.39 kg)
Bulk Cable Weight:	17 lbs/1000ft

## Standards and Compliance

Environmental Suitability:	Indoor - Riser, Indoor
Flammability / Reaction to Fire:	UL1666 Riser, FT4
NEC / UL Compliance:	Article 800, CMR
CEC / C(UL) Compliance:	CMG
European Directive Compliance:	EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)

## History

Update and Revision:	Revision Number: 0.326 Revision Date: 09-07-2025
----------------------	--

## Part Numbers

### Variants

Item #	Color	Putup Type	Length	UPC	Footnote
1175A 0021000	Red	Reel	1,000 ft	612825107859	C
1175A 0025000	Red	Reel	5,000 ft	612825107873	C
1175A 0026600	Red	Reel	6,600 ft	612825107880	C
1175A 00210000	Red	Reel	10,000 ft	612825107866	C

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.