

Product: [1862A](#) 



Speaker Cable, 2 Conductor 16 AWG BC, Unshielded, CMP

Product Description

Speaker Cable, 2 Conductor 16 AWG stranded (19x29) high conductivity bare copper conductors with Flamarrest® insulation, cabled in an open twisted construction, Plenum-CL3P.

Technical Specifications

Product Overview

Suitable Applications:	Speaker Cable
------------------------	---------------

Construction Details

Conductor

Size	Stranding	Material
16	19x29	BC - Bare Copper

Insulation

Material
PVC - Polyvinyl Chloride

Outer Shield

Material
No Shield

Outer Jacket

Nom. Diameter
0.202 in

Electrical Characteristics

Voltage

UL Voltage Rating
150 V RMS

Mechanical Characteristics

Temperature

Operating
-20°C To +75°C

Max. Pull Tension:	60.8 lbs (27.6 kg)
Bulk Cable Weight:	24 lbs/1000ft (36 kg/km)

Standards and Compliance

Environmental Suitability:	Indoor - Plenum, Indoor
Flammability / Reaction to Fire:	NFPA 262
NEC / UL Compliance:	CL3P
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)

History

Update and Revision: Revision Number: 0.352 Revision Date: 09-07-2025

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC	Footnote
1862A D261000	Black & Natural Pair	Reel	1,000 ft	612825125167	C

Footnote: C - CRATE REEL PUT-UP.

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.