



Product: [1936/4](#) 

CORDS, 4C #14, Str, Neoprene, 600 V, SOOW 90C, CSA C(UL) SOOW, CSA C(UL) FT2

Product Description

CORDS, 4 Conductor 14 AWG (41/30) BC - Bare Copper, Neoprene Insulation, Black Chlorinated Polyethylene (CPE) Outer Jacket, SOOW 90C, CSA C(UL) SOOW, CSA C(UL) FT2 C(UL) SOOW, C(UL) FT2

Technical Specifications

Product Overview

Suitable Applications:	Data, communication, audio, and low-level signal transmission; industrial networking, serial communication, control panels, automation equipment, and instrumentation systems.
------------------------	--

Construction Details

Conductor

Element	No. of Elements	Size	Stranding	Material
Conductor(s)	4	14 AWG	41x30	BC - Bare Copper

Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Conductor(s)	Neoprene	0.048 in (1.2 mm)	0.173 in (4.39 mm)	Black, White, Red, Green

Outer Jacket

Material	Nom. Thickness	Nom. Diameter
CPE - Chlorinated Polyethylene	0.085 in (2.2 mm)	0.596 in (15.1 mm)

Overall Cable Diameter (Nominal):	0.596 in (15.1 mm)
-----------------------------------	--------------------

Electrical Characteristics

Electricals

Element	Nom. Capacitance Cond-to-Cond	Nom. Inductance
Conductor(s)	36 pF/ft (120 pF/m)	0.22μH/ft. μH/ft

Voltage

UL Voltage Rating
600 V (SOOW)

Mechanical Characteristics

Temperature

UL Temperature	Operating
90°C	-40°C To +90°C

Bend Radius

Stationary Min.
6.0 in (150 mm)

Max. Pull Tension:	61 lbs (28 kg)
--------------------	----------------

Standards and Compliance

Environmental Suitability:	Indoor, Outdoor
Flammability / Reaction to Fire:	FT2
European Directive Compliance:	EU Directive 2015/863/EU (RoHS 2 amendment), REACH, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)

Product Notes

Notes:	Alpha Wire -* P/N 1936/4 4C 14 AWG (UL) C(UL) TYPE SOOW 90C 600V -40C FT2 CE ROHS
--------	---

History

Update and Revision:	Revision Number: 0.13 Revision Date: 06-30-2026
----------------------	---

Part Numbers

Variants

Item #	Color	Putup Type	Length
1936/4 BK003	Black	Reel	250 ft

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.