



Product: [37102](#) 

Lead Wire, #2 Str TC, EPDM Ins, AWM 3340 AWM 3374

 [Request Sample](#)

Product Description

Rubber Lead Wire, 2AWG (163x24) Tinned Copper, EPDM Insulation, AWM 3340 AWM 3374 CSA TYPE CL1254 600V 125C FLEX 150C NO FLEX

Technical Specifications

Product Overview

Suitable Applications:	Class 130(B), 155(F) and also in some 180(H) motor lead systems, high temperature, internal wiring of appliances
------------------------	--

Construction Details

Conductor

Element	No. of Elements	Size	Stranding	Material
Conductor(s)	1	2 AWG	163x24	TC - Tinned Copper

Insulation

Material	Nom. Thickness	Nom. Insulation Diameter
EPDM - Ethylene Propylene Diene Monomer	0.088 in (2.2 mm)	0.494 in (12.5 mm)

Overall Cable Diameter (Nominal):	0.494 in (12.5 mm)
-----------------------------------	--------------------

Electrical Characteristics

Electricals

Nom. Conductor DCR	Max. Current
0.172 Ohm/1000ft	256 Amps per Conductor at 30°C

Voltage

UL Voltage Rating
600 V (AWM 3340, AWM 3374)

Mechanical Characteristics

Temperature

UL Temperature	Operating
150°C	-55°C To +150°C

Bend Radius

Stationary Min.	Installation Min.
4.94 in (125 mm)	4.94 in (125 mm)

Max. Pull Tension:	824.6 lbs (374.0 kg)
Bulk Cable Weight:	276 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor, Outdoor
Sustainability:	CA Prop 65
Flammability / Reaction to Fire:	Horizontal flame
AWM Compliance:	AWM 3340, AWM 3374

CEC / C(UL) Compliance:	CL-1254
European Directive Compliance:	EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)

Product Notes

Notes:	Separator Material over Conductor: Y
--------	--------------------------------------

History

Update and Revision:	Revision Number: 0.490 Revision Date: 09-07-2025
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC	Footnote
37102 010100	Black	Reel	100 ft	612825146650	C
37102 010250	Black	Reel	250 ft	612825146674	C F
37102 0101000	Black	Reel	1,000 ft	612825146667	C
Footnote:		C - CRATE REEL PUT-UP., F - MAY CONTAIN MORE THAN 1 PIECE. MINIMUM LENGTH OF ANY ONE PIECE IS 50'.			

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.