



Product: [5202U1](#) 

Security & Sound, #16-4c, TC, CMG, Water-blocked

Product Description

Security & Sound Cable, CMG, 4-16 AWG stranded tinned copper conductors with PVC, Waterblocking tape and PVC jacket with ripcord

Technical Specifications

Product Overview

Suitable Applications:	Security System, Intercom/PA, Audio/Speaker, Power-Limited Controls, Wet Location, Below-Grade Duct
------------------------	---

Construction Details

Conductor

Element	No. of Elements	Size	Stranding	Material
Conductor(s)	4	16	7x24	TC - Tinned Copper

Insulation

Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
PVC - Polyvinyl Chloride	0.017 in (0.43 mm)	0.09 in (2.3 mm)	Black, White, Red, Green

Waterblocking:	Waterblock Tape
----------------	-----------------

Outer Jacket

Separator	Material	Nom. Thickness	Nom. Diameter
Waterblocking Tape	PVC - Polyvinyl Chloride	0.042 in (1.1 mm)	0.337 in (8.56 mm)

Electrical Characteristics

Electricals

Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Max. Current
4.35 Ohm/1000ft (14.3 Ohm/km)	33 pF/ft (110 pF/m)	9 Amps per Conductor at 25°C

Voltage

UL Voltage Rating
300 V

Mechanical Characteristics

Temperature

UL Temperature	Operating
90°C	-20°C To +90°C

Bend Radius

Stationary Min.	Installation Min.
3.37 in (85.6 mm)	3.37 in (85.6 mm)

Max. Pull Tension:	142 lbs (64.4 kg)
Bulk Cable Weight:	67 lbs/1000ft (100 kg/km)

Standards and Compliance

Environmental Suitability:	Indoor, Outdoor, Sunlight Resistance, Oil Resistance, Burial
----------------------------	--

Flammability / Reaction to Fire:	UL1685 FT4 Loading, FT4, IEEE 1202 Vertical Tray Flame Test
NEC / UL Compliance:	Article 725, Article 760, Article 800, CMG, FPL, PLTC
CEC / C(UL) Compliance:	CMG
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)

History

Update and Revision:	Revision Number: 0.539 Revision Date: 02-03-2026
----------------------	--

Part Numbers

Variants

Item #	Color	UPC	Footnote
5202U1 0101000	Black	612825158172	C

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.