



Product: [530BUE](#) 

Security & Sound, #18-20c, BC, CMR

Product Description

Security & Sound Cable, Riser-CMR, 20-18 AWG stranded bare copper conductors with PVC insulation, PVC jacket with ripcord

Technical Specifications

Product Overview

Suitable Applications:	Security System, Intercom/PA, Audio/Speaker, Power-Limited Controls
------------------------	---

Construction Details

Conductor

Element	No. of Elements	Size	Stranding	Material
Conductor(s)	20	18 AWG	7x26	BC - Bare Copper

Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Conductor(s)	PVC - Polyvinyl Chloride	0.01 in (0.25 mm)	0.066 in (1.7 mm)	Black, Red, White, Green, Brown, Blue, Orange, Yellow, Purple, Gray, Pink, Tan, White/Black, White/Red, White/Green, White/Orange, White/Blue, White/Brown, White/Yellow, White/Violet

Outer Shield

Material
No Shield

Outer Jacket

Material	Nom. Thickness	Nom. Diameter	Ripcord
PVC - Polyvinyl Chloride	0.025 in (0.64 mm)	0.4 in	Yes

Overall Cable Diameter (Nominal):	0.4 in
-----------------------------------	--------

Electrical Characteristics

Electricals

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Max. Current
Conductor(s)	6.5 Ohm/1000ft	30 pF/ft (98 pF/m)	2.5 Amps per Conductor at 25°C

High Frequency (Nominal/Typical)

Nom. Insertion Loss (Attenuation) [dB/100m]
26.4

Voltage

UL Voltage Rating
300 V

Mechanical Characteristics

Temperature

UL Temperature	Operating
75°C	-20°C To +75°C

Bend Radius

Stationary Min.	Installation Min.
4.0 in (100 mm)	4.0 in

Max. Pull Tension:	448 lbs (203 kg)
Bulk Cable Weight:	144 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor
Flammability / Reaction to Fire:	UL1666 Riser, FT4, IEC 60332-1-2
CPR Compliance:	CPR Euroclass: Eca
NEC / UL Compliance:	Article 800, CMR
CEC / C(UL) Compliance:	CMG.
European Directive Compliance:	EU CE Mark, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)

History

Update and Revision:	Revision Number: 0.302 Revision Date: 09-07-2025
----------------------	--

Part Numbers

Variants

Item #	Color	UPC
530BUE 0081000	Gray	612825158943

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.